E2460PDA

24 inch (61 cm) LCD MONITOR

Verbluffende prestaties die comfort op de eerste plaats stellen

5ms

ADJUSTABLE STAND

FHD

SPEAKERS

VESA MOUNT



Ingebouwde Speakers

Ingebouwde luidsprekers maken bijpraten met familie vrienden en collega's gemakkelijk. Voor films, muziek, games en meer, geniet u van kwaliteitsaudio zonder het gedoe van het aansluiten van externe luidsprekers.

In de hoogte verstelbare standaard

Wij geven om uw welzijn. Daarom biedt deze monitor opties voor aanpassingen in de hoogte, door middel waarvan u de volmaakte houding kunt vinden tijdens het werken, spelen of kijken naar video's. Door uw AOC-monitor aan uw wensen aan te passen kunt u niet alleen de vermoeidheid terugdringen en uw lichaam gezond houden. Uiteindelijk laat het u en uw team betere resultaten bereiken bij wat u ook aan het doen bent.



5ms pixelresponstijd

Een pixelresponstijd van 5 ms GTG betekent snelheid zonder vegen op het scherm en geeft een verbeterde gaming-ervaring. Snel bewegende actie en dramatische overgangen worden gelijkmatig weergegeven zonder de vervelende effecten van ghosting. Kies het juiste pad naar succes, laat u niet tegenhouden door een langzame display.

Kensington Lock

Kensington Lock is een anti-diefstalsysteem, dat bestaat het uit een met metaal versterkt gat in de behuizing van het toestel, zodat het met een metalen kabel en een systeem met een sleutel/vergrendeling kan worden gebruikt. Met Kensington Locks kunt u uw AOC-monitor veilig vastzetten tijdens een LAN-evenement, een bijeenkomst of waar u uw monitor maar naartoe brengt.

General

Model name	E2460PDA
EAN	4038986141963
Product Line	Pro-line
Series	60 Series
Channel	B2B
Classification	Mainstream
Section	Bedrijf
Launch date	28-12-2014

Screen

Resolution	1920x1080
Refresh rate	60Hz
Screen size (inch)	24 inch
Screen size (cm)	61 cm
Backlight	WLED
Panel Type	TN
Aspect ratio	16:9
Display Colours	16,7 miljoen
Active Screen Area (HxW)	531,36x298,89 mm mm
Pixel Pitch	0.276
Scanning Frequency	30-83khz/50-76hz
Pixel Frequency	148.5MHz
Response time (GtG)	5 ms
Contrast (static)	1000:1
Contrast (dynamic)	50M:1
Brightness (typical)	250 cd/m²
Viewing angle (CR10)	170/160 º
OSD languages	EN, FR , ES, PT, DE, IT, NL, SE, FI, PL ,CZ, RU, KR, CN (T), CN (S), JP

Exterior

Monitor colour	Zwart
Bezel Type	Normaal

Ergonomics

Vesa Wallmount	100x100
Tilt	-5/20 °
Swivel	-165/165 °
Pivot	✔
Height Adjust Amount	130mm

Multimedia	
Built-in Speakers	2 W x 2

Connectivity and Multimedia	
Signal Input	VGA, DVI

What's in the Box?	
VGA cable	1,8 m
DVI cable	1,8 m
Audio Cable	1,8 m
Power Cable C7	1.8 m

Power / Environmental	
Powersupply	Intern
Powersource	100 - 240 V 50/60 Hz
PowerConsumption On (Energystar)	18.54 watt
PowerConsumption Standby (Energystar)	0.29 watt
PowerConsumption Off (Energystar)	0.13 watt

Approbations / Regulations	
TCO	6
EPEAT	Yes
TUV-GS	✔
CE	✔
FCC	✔
EAC	✔
Rohs compliant	✔
other documentation	EPA Report

Warranty	
Pixel Policy	ISO 9241-307
Warranty Period	3 Jaar
MTBF	50.000 uur

Dimensions / Weights	
Product height (mm)	393.6
Product width (mm)	565.4
Product depth (mm)	244.58
Packaging Dimensions (L x W x H)	693x423x187 mm
Product Dimensions (incl base)	565.4x393.6x244.58 mm
Gross Weight (including package)	8.55 Kg
Net Weight (excluding package)	6.54 Kg

Texts and USP	
Marketing title	24 inch 1920x1080@60Hz 5 ms TN VGA, DVI