EXPERIENCE THE POWER OF THE PEN
TABLET PCS



LIFEBOOK T900 - YOUR ULTIMATE MOBILE MEETING TOOL

The LIFEBOOK T900 is an ultra versatile lightweight convertible notebook for the professional user. Its bi-directional, rotatable, wide-view, high-bright LED display is a pleasure to use. With the LIFEBOOK T900 multiple touch you can either work with your fingers or with the patented multifunctional pen. Berliner Glass ensures the highest reliability.

LIFEBOOK T4410/T4310 – TWIST TO TOUCH

The LIFEBOOK T4410 and LIFEBOOK T4310 offer all the benefits of an ultraportable convertible with multiple touch capability. Scroll through documents, zoom into graphics or move files and folders – all with your fingertip. Working with a notebook has never been more intuitive and easier. Enjoy the advantages of flexible pen based data input. Like handwriting recognition and lots of additional features, that only a convertible notebook offers.

STYLISTIC ST6012 - THE IDEAL MOBILE SOLUTION FOR INDOORS AND OUTDOORS

The STYLISTIC ST6012 is the perfect companion for indoor and outdoor work and was specially developed for use when standing or walking. The device weighs only 1.6 kg, is very easy to carry and comes in a semi-ruggedized design while the transmissive 30.7 cm (12.1-inch) TFT WXGA display offers best image quality.

Contact
Email: clients.info@ts.fujitsu.com
Internet: ts.fujitsu.com/tabletpc
Extranet: partners.ts.fujitsu.com/tabletpc
2010-01-CE-EN

Copyright
© Fujitsu Technology Solutions 2010

All hardware and software names used are brand names and/or trademarks of their respective holders.

MINI	ALL-ROUND	ADVANCED	SUPERIOR
Internet	Standard Home and Office Application	Entertainment, Mobile Office	Ultimate Computing for Individual Needs
FUJITSU M2010	LIFEBOOK P3110	ESPRIMO Mobile U,M,D,X	LIFEBOOK T730
•Available in 3 different colors •Compact size/ weight •From 1.2 kg	•Optional 3G/ UMTS •Energy efficient components (CPU, LED) •Available in 3 different colors •From 1.49 kg	•Optional 3G/UMTS •Family concept (modular bay, portrep, AC adapter) •Ultimate security •Long battery runtime •From 1.95 kg	•Convertible/ Tablet PC •Optional 3G/ UMTS •Ultimat security (incl. ATP*) •Active/ passive /dual digitizer* •Berliner glass option •From 1.6 kg

ALL-ROUND	ADVANCED	SUPERIOR
		Ultimate Computing for Individual Needs
ESPRIMO Mobile V	LIFEBOOK AH550	AMILO Pi 3x60	LIFEBOOK NH570	LIFEBOOK S710	LIFEBOOK E780 int. graphics	LIEFBOOK P770	LIFEBOOK S760, E780 ext. graphics	STYLISTIC/ LIFEBOOK T	CELSIUS H
•Dedicated performance graphics card* •Optional 3G/UMTS •Available in 5 different colors or black edition •From 2.75 kg	•Reliable and solid design •Spill-resistant keyboard •Optional 3G/UMTS •From 2.75 kg	•Dedicated performance graphics card* •Comfortable working due to silent mode function •Spill-resistant keyboard •From 2.75 kg	•Appealing design •Optional Blue-ray Disc™ drive •Optional graphics card •From 3.5 kg	•Slim and lightweight design •Variety of interfaces •Optional 3G/UMTS •Long battery runtime •From 2.1 kg	•Unbeatable number of interfaces •Optional 3G/UMTS •Long battery runtime •From 2.7 kg	•Stylish, ultra-portable design •Ultimate mobility •Ultimat security (incl. ATP*) •Small footprint •Long battery runtime •From 1.4 kg	•Optional 3G/UMTS •Ultimate security (incl. ATP*) •Compact size/ weight •Long battery runtime •From 1.6 kg	•Convertible/ Tablet PC •Optional 3G/ UMTS •Ultimat security (incl. ATP*) •Active/ passive /dual digitizer* •Berliner glass option •From 1.6 kg	•Dedicated high performance graphics card •Optional 3G/UMTS •Ultimate security •CAD, DCC, VIS certified •From 2.75 kg Read more: ts.fujitsu.com/workstation-positioning

* depending on model

ARE YOU INTERESTED IN OUR COMPREHENSIVE NOTEBOOK PORTFOLIO?
➡ Link: ts.fujitsu.com/notebook-positioning
DO YOU NEED EVEN MORE EXPANDABILITY, MORE PERFORMANCE AND OUTSTANDING GRAPHICS?
➡ Link: ts.fujitsu.com/workstation-positioning
DO YOU NEED MAINTENANCE AND SERVICE SUPPORT?
➡ Link: ts.fujitsu.com/servicepositioning

EXPERIENCE THE POWER OF THE PEN
TABLET PCS

FUJITSU

	SUPERIOR			
	STYLISTIC ST6012	**LIFEBOOK T900**	**LIFEBOOK T4410**	**LIFEBOOK T4310**
Category	Tablet PC - Slate	Tablet PC - Convertible		
Processor (Up to)	Intel® Core™2 Duo	Intel® Core™i7	Intel® Core™2 Duo	
Chipset	Intel® GS45	Intel® QM57	Intel® GM45	
Display	30.7 cm (12.1-inch) WXGA, active digitizer	33.8 cm (13.3-inch) WXGA, active or dual digitizer	30.7 cm (12.1-inch) WXGA, dual digitizer	30.7 cm (12.1-inch) WXGA, dual digitizer
Graphics	Mobile Intel® GMA 4500M HD	Intel® HD Graphics	Mobile Intel® GMA 4500M HD	
Weight	1.6 kg[1)]	2.0 kg[1)]	1.79 kg[1)]	1.79 kg[1)]
Communication (LAN included)	Optional 3G/UMTS, WLAN, Bluetooth			
Webcam (optional)	1.3 Mpx	2.0 Mpx	1.3 Mpx	
Modularity	-	DVD drive, second battery, second HDD		
Battery life (1st/2nd)	Up to 9 h[2)]	Up to 7 / 11 h[2)]	Up to 6 / 9 h[2)]	Up to 5 / 8 h[2)]
Port replicator	Dedicated	Dedicated	Dedicated	-
Spill-resistant keyboard	-	•	•	•
ShockSensor	•	•	•	•
EcoButton	-	•	•	•
ATP	-	•	-	-
Fingerprint sensor	•	•	•	•
Ambient light sensor	-	•	•	•

1) Weight may vary depending on actual configuration 2) Battery life may vary depending on product model, configuration, applications, power management settings and features utilized. Battery rechardge time depends on usage