SPECIFICATIONS

PANEL SIZE	23.8"
PANEL RESOLUTION	1920 x 1080 (FHD)
REFRESH RATE	75Hz
RESPONSE TIME	5ms (GTG)
PANEL TYPE	IPS
VIEWING ANGLE	178°(H) / 178°(V)
ASPECT RATIO	16:9
CONTRAST RATIO	1000:1
sRGB	100% (CIE 1976)
ACTIVE DISPLAY AREA (MM)	527.04(H) x 296.46(V)
PIXEL PITCH (H X V)	0.2745(H) x 0.2745(V)
SURFACE TREATMENT	Anti-glare
DISPLAY COLORS	16.7M
COLOR BIT	8 bits
VIDEO PORTS	1x HDMI (1.4) 1x DP (1.2a)
AUDIO PORTS	1x Headphone-out
KENSINGTON LOCK	Yes
SPEAKER	2x 2W
VESA MOUNTING	75 x 75 mm
POWER TYPE	External Adaptor (12V 2.5A)
POWER INPUT	100~240V, 50~60Hz
ADJUSTMENT (TILT)	-5° ~ 20°
DIMENSION (W X H X D)	541.93 x 421.79 x 182.16 mm (21.34 x 16.61 x 7.17 inch)
WEIGHT (NW / GW)	2.95 kg (6.5 lbs) / 4.15 kg (9.15 lbs)
Compatibility	PC, Mac, PS5™, PS4™, Xbox, Mobile, Notebook * All trademarks and the registered trademarks are the property of their respective owners.
Note	HDMI: 1920 x 1080 (Up to 75Hz) D-Sub: 1920 x 1080 (Up to 60Hz)

FEATURES

23.8" Screen Size
View your applications, spreadsheets and more with a perfect 23.8 inches screen

IPS Grade Panel
Instantly optimize the screen colors and brightness to ensure that you enjoy every detail at its best while creating your own on-line video

75Hz High Refresh Rate
Experience smooth gaming with a blazing fast 75Hz refresh rate, that gives you the upperhand in fast moving games.

Anti-Glare Display Design

An anti-glare display makes viewing the display more pleasant for users and reduces eyestrain for users

Less Blue Light
Effectively reduce blue light which could cause serious long-term damage to your eyes.

Display Kit Support
Providing the most convenient tool, the proper color & display mode to you while working with it everyday.

VESA Mountable
To be mounted on the wall of your office & home with a VESA standard design which can make it completely invisible on a desk.

Built-In Speaker
Built-in speakers allow you to listen clearly without connecting external speakers.

CONNECTIONS

1. 1x DisplayPort
2. 1x HDMI
3. 1x Headphone-out
4. 1x DC Jack
5. 1x Kensington Lock