ThinkPad T14 Gen 3 (Intel)

Designed for the modern workforce who need to work from anywhere, this compact desktop is a powerhouse of modern features. It has up to 12th Gen Intel Core processor and multiple display options with technologies like low power consumption, anti-glare, and anti-smudge to choose from. With its onboard Intel UHD graphics and discrete NVIDIA GeForce, combined with up to 2TB ultra-fast SSD storage, it delivers quicker responsiveness while working on heavy-duty applications and complex data or files.

Comes with a slew of ports, including 2x USB 3.2 Gen 1. Users can connect up to 3 external monitors via Thunderbolt and HDMI ports for seamless multitasking. WiFi 6 support enables faster uploads and downloads as well as lower latency when used with compatible routers.

Security solutions include an optional IR camera for Windows Hello for facial recognition, an optional web camera shutter for user privacy during calls or meetings, and a Kensington slot for device safety.

Minimal preloaded applications mean maximum battery life and responsiveness for users, and faster deployment for IT admins.

Lenovo devices that are a class apart

The ultimate productivity notebook, ThinkPad T Series will keep users productive all day with long battery life, docking and enhanced connectivity options, security and manageability features.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..

Premier Support

Talk directly with advanced technical support agents
Support for software & hardware
Next business day onsite repairs

Accessories

Lenovo Powered USB-C Travel Hub

Connects to a PC through a single USB-C cable which also recharges the device
Connect to an external display with HDMI or VGA, and other peripherals with 2x USB ports
Compact 183x100mm (7.2x4") design with integrated cable management

PN: 4X90S92381

Lenovo 700 Ultraportable Bluetooth Speaker

Just 11mm (0.43") thin and weighing 145g (0.32lb), this ultra-thin Bluetooth speaker delivers 360-degree sound with 2x 2Watt power output
Supports Siri and Google Assistant voice commands for your iOS and Android devices, as well as a dedicated button for taking calls
Fast-charges in 2 hours and lasts for up to 12hours of audio playback or voice calls

PN: 4XD0T32974

ThinkPad T14 Gen 3 (Intel)

Performance

Processor
12th Gen Intel U or P Series Core i5 / i7

Operating System
Windows 11 Pro
Windows 11 Home
Windows 11 Home Single Language
Windows 11 DG Windows 10 Pro 64
Linux
Ubuntu Linux

Graphics [1]
Intel Iris Xe Graphics eligible (integrated)
NVIDIA GeForce MX550

[1]Intel Iris Xe Graphics capability requires system to be configured with dual-channel memory. On the system with single-channel memory, Intel Iris Xe Graphics will function as Intel UHD Graphics.

Memory [2]
Up to 40GB or 48GB DDR4-3200, 1x Soldered + 1x SO-DIMM

[2]The max memory is based on the test results with current Lenovo memory offerings.

Storage [3]
Up to 1x 2TB M.2 2280 PCIe NVMe SSD

[3]The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio
High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Audio
Dual-microphone array, far-field, Dolby Voice*

Camera
HD 720p, with privacy shutter
FHD 1080p, with privacy shutter
FHD 1080p + IR hybrid, with privacy shutter

Battery [4]
39.3Wh or 52.5Wh battery, up to 10.0 hr, Rapid Charge

[4]Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

Power Adapter
45W USB-C adapter, PD 3.0
65W USB-C adapter, PD 3.0
65W USB-C slim adapter, PD 3.0

Design

Display [5]
14" WUXGA (1920x1200) IPS Anti-glare 16:10
- 300nits, 45% NTSC
- 300nits, 45% NTSC, touch
- 400nits, 100% sRGB, low power, Eyesafe
- 500nits, 100% sRGB, touch, ThinkPad Privacy Guard

14" 2.2K (2240x1400) IPS Anti-glare 16:10
- 300nits, 100% sRGB, Eyesafe

14" WQUXGA (3840x2400) IPS ARAS 16:10
- 500nits, 100% DCI-P3, DisplayHDR 400, Dolby Vision, Eyesafe

[5]IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard
6-row, spill-resistant, optional backlight

Touchpad
TrackPoint and glass-like Mylar surface touchpad
61 x 115 mm (2.40 x 4.53 inches)

Dimensions [6]
Models with storm grey cover:
317.7 x 227.36 x 17.9 mm (12.51 x 8.95 x 0.70 inches)
Models with black cover:
317.7 x 226.9 x 17.9 mm (12.51 x 8.93 x 0.70 inches)

[6]The system dimensions may vary depending on configurations.

Weight [7]
Starting at 1.358 kg (2.99 lbs)

[7]The system weight is approximate and may vary depending on configurations

Color
Storm grey
Thunder black

Case material
Aluminium (top), PPS (bottom)
PC + 20% CF + 50% GF (top), PPS (bottom)
PC + 20% CF + 50% GF (top), aluminium (bottom)

Connectivity

Ethernet
Gigabit onboard Ethernet

WLAN + Bluetooth [8 9]
802.11ax (Wi-Fi 6E), Bluetooth 5.1
Up to Intel Wi-Fi 6E AX211, Bluetooth 5.1

[8]Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitations.

[9]Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

WWAN
4G LTE CAT4
4G LTE CAT16

NFC
Near Field Communication*

Ports
1x USB 3.2 Gen 1
1x USB 3.2 Gen 1 (Always On)
2x Thunderbolt 4 / USB4 40Gbps (data, PD 3.0, DP 1.4)
1x HDMI 2.1, up to 4K/60Hz
1x Ethernet (RJ-45)
1x Headphone / microphone combo jack (3.5mm)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking
Docking support via Thunderbolt or USB-C

Security & Privacy

Discrete TPM 2.0
Kensington Nano Security Slot
Smart card reader*
Touch style MOC fingerprint reader*
Camera privacy shutter*
IR camera for Windows Hello*
Privacy Guard with Privacy Alert*
Human Presence Detection (software)
Glance by Mirametrix
RFID reader*

Manageability

Intel vPro Enterprise
Intel vPro Essentials

[10]Intel vPro offers a superset of DASH's defined capabiliti

Certifications

Green Certifications [11 12]
ENERGY STAR 8.0*
EPEAT Gold Registered*
ErP Lot 3
TCO Certified 9.0
RoHS compliant

[11]The items listed under the "Green Certifications" section may not only refer to certification but also registration o self-declaration.

[12]EPEAT is registered where applicable, please see https://www.epeat.net for registration status by country

Other Certifications
Eyesafe Certified*
MIL-STD-810H

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2023 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.