BI WDHG 961485 UK

12NC: 869991664080

GTIN (EAN) code: 5054645664085



MAIN FEATURES

Product group	Washer dryer
Commercial code	BI WDHG 961485 UK
GTIN (EAN) code	5054645664085
Construction type	Built-in
Installation type	Free-standing
Removable work top	No
Loading type	Front loader
Main colour of product	White
Electrical connection rating (W)	1850
Current (A)	13
Voltage (V)	220-240
Frequency (Hz)	50
Length of electrical supply cord (cm)	120
Plug type	UK
Height of the product	815
Width of the product	595
Depth of the product	545
Depth with open door 90 degree (mm)	-
Net weight (kg)	66

TECHNICAL FEATURES

Automatic programmes	Yes
Moisture monitoring system	Yes
Adjustable drying temperature	No
Progress indicator	DISPLAY
Digital countdown indicator	No
Start delay options	Continuous
Start delay time max. (h)	0
Blocked filter indicator	No
Quick dry	No
Anti-crease function	No
Drum volume (l)	58

PERFORMANCES

Energy Efficiency Class Eco 40-60 programme (Regulation (EU) 2017/1369)	B
Energy Efficiency Class Wash/Dry cycle(Regulation (EU) 2017/1369)	D
Spin-drying efficiency class (EU 2017/1369)	B
Maximum mass in kg that can be treated in a wash cycle (EU 2017/1369)	9,0
Maximum mass in kg that can be treated in a wash and dry cycle (EU 2017/1369)	6,0
Airborne acoustical noise emissions (EU 2017/1369)	70
Airborne acoustical noise emission class (EU 2017/1369)	A
Weighted remaining moisture content (D) (EU 2017/1369)	53,0
Weighted energy consumption in kWh per 100 full wash and dry cycles. Energy Label (EU 2017/1369)	307
Weighted energy consumption in kWh per 100 washing cycles. Energy Label (EU 2017/1369)	56
Energy consumption in kWh per cycle of Wash/Dry eco 40-60 programme (EU 2017/1369)	3,072
The water consumption of the full wash and dry cycle in liters per cycle (EU 2017/1369)	65
Duration of the full wash and dry cycle at rated capacity in HMM (EU 2017/1369)	9:20