FPMA-HAC100HC

NEOMOUNTS BY NEWSTAR MEDICAL CEILING

Neomounts by Newstar Medical Monitor Ceiling Mount (Full Motion gas spring) for 10"-32" Screen, Height Adjustable - White

SPECIFICATIONS

Color	White
Depth	0 - 189 cm
Height	0 - 170 cm
Height adjustment	Gasspring
Max. screen size	32
Max. weight	12
Min. screen size	10
Min. weight	6
Pivot points	3
Screens	1
Swivel (degrees)	370°
Tilt (degrees)	55°
Type	Full motion
	Tilt
	Swivel
VESA maximum	100x100 mm
VESA minimum	75x75 mm
VESA pattern	100x100
	75x75
Warranty	5 year
EAN code	8717371443177

The Neomounts by Newstar ceiling mount, model FPMA-HAC100HC is a tilt- and swivel ceiling mount for medical flat screens up to 32?. This mount is a great choice for space saving placement or when wall mounting and floor placement is not an option.

Neomounts by Newstar's versatile tilt (55°) and swivel (370°) technology allows the mount to change to any viewing angle to fully benefit from the capabilities of the flat screen. The support is easily height adjustable from 0 to 170 centimetres using a gas spring. Depth adjustable from 0 to 170 centimetres. An innovative cable management conceals and routes cables from mount to flat screen. Hide your cables to keep the workplace nice and tidy.

Neomounts by Newstar FPMA-HAC100HC has two pivot points and is suitable for screens up to 32" (81 cm). The weight capacity of this product is 12 kg each screen. The ceiling mount is suitable for screens that meetVESA hole pattern 75x75 or 100x100mm. Different hole patterns can be covered using Neomounts by Newstar VESA adapter plates.

All installation material is included with the product.

Neomounts®
BY NEWSTAR

FPMA-HAC100HC NEOMOUNTS BY NEWSTAR MEDICAL CEILING