UNIFIED COMMUNICATIONS

INFORMATION

Stylish and discreet Professional 4K Webcam with Built in microphone, 5x Digital zoom, 120° field of view (FoV) and Auto Tracking

This stylish, professional 4K webcam with 5x Digital Zoom and built in microphone will take your video conferences to the new level. With a 120° field of view and 5x zoom, the UC-CAM10PRO-1 provides a sensational, smooth, and detailed picture. The webcam has two built-in microphones that detect sound from up to 4 meters away, so you can be sure everyone will be heard during the meetings. This compact-size camera with a privacy cover will be a perfect match for any space - whether it's a small huddle space or meeting room. With a 14° tilt adjustment feature, the camera can be customized to fit your needs and adapt to your individual space.

120° field of view

The field of view means the observable area one can see through the camera lens. It translates directly to how much of your meeting space will be visible to the participants joining remotely. A 120-degree FoV is the right solution for most standard meeting spaces.

2D & 3D Digital Noise Reduction

Delivering high image quality, these two image denoising technologies combined ensure crisp and clear visuals for video and photos.



Auto-framing

With intelligent face detection and voice localization, the camera tracks whoever is speaking and smoothly switches between presenters automatically adjusting to best fit participant location and quantity. It not only recognizes and zooms in on meeting participants, but also tracks speakers as they move about the room.

Clear, crisp and natural audio

Featuring an advanced noise reduction algorithm, the integrated 2-element mic array detects audio from up to 4 metres away, delivering high quality audio free from any annoying background noise or distortion.

SPECIFICATION

01 CAMERA

Pixels	8,46M
Native resolution	4K UHD
Supported resolutions	2160p/30fps, 1440p/30fps, 1080p/30fps
Diagonal field of view (dFoV)	120°
Focus mode	fixed
Focus distance	8m
Aperture	2.5
Zoom	5x digital zoom
White balance	yes
Exposure	yes
Backlight compensation	yes
AutoFraming	yes

02 AUDIO

Number of microphone arrays	2
Voice pickup distance	4m
Voice pickup angle	180°
Noise reduction	yes
Automatic gain control	yes

03 CONNECTIVITY

Camera	USB Type-C
Host	USB v.3.0

04 MICROPHONE

Number of microphone arrays	x2
Voice pickup range	4m (radius)

05 CONNECTIVITY & BUTTON OPERATIONS

USB Type C	x1

06 MECHANICAL

Tilt angle	≤14°
Rotation	360°
Privacy shutter	yes

07 ACCESSORIES INCLUDED

Cables	USB 2.0 (type A to C)
Anti peeping cover	yes
Remote control	yes (batteries included)
Power adapter	yes

08 SUSTAINABILITY

Regulations	CE, RoHS support, ErP, WEEE, REACH, UKCA

09 DIMENSIONS / WEIGHT

Product dimensions W x H x D	80 x 75 x 53mm
Box dimensions W x H x D	162 x 124 x 90mm
Weight (without box)	0.21kg
Weight (with box)	0.5kg
EAN code	4948570033140

GALLERY



All trademarks and registered trademarks acknowledged. E & O E. Specification subject to change without notice. All LCD's comply with ISO-9241-307:2008 in connection with pixel defects. **© IIYAMA CORPORATION. ALL RIGHTS RESERVED**