Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2016 with regard to energy labelling of refrigerating appliances

Supplier's name or trade mark: Samsung

Supplier's address: Public Contact, Samsung PO Box 12987 Blackrock Co.Dublin Ireland

Model identifier: RB34C671DS9

Type of refrigerating appliance:

Low-noise appliance:	No	Design type:	freestanding
Wine storage appliance:	No	Other refrigerating appliance:	No

General product parameters:

Parameter		Value	Parameter	Value
Overal dimensions (millimetre)	Height	1 853	Total volume (dm³ or l)	344
	Width	595		
	Depth	658		
EEI		80	Energy efficiency class	D
Airborne acoustical noise emissions (dB(A) re 1 pW)		35	Airborne acoustical noise emission class	B
Annual energy consumption (kWh/a)		204	Climate class:	extended temperate, temperate, subtropical, tropical
Minimum ambient temperature (ºC), for which the refrigerating appliance is suitable		10	Maximum ambient temperature (ºC), for which the refrigerating appliance is suitable	43
Winter setting		No		

Compartment Parameters:

Compartment type	Compartment parameters and values			
	Compartment Volume (dm³ or l)	Recommended temperature setting for optimised food storage (ºC) These settings shall not contradict the storage conditions set out in Annex IV, Table 3	Freezing capacity (kg/24h)	Defrosting type (auto-defrost=A, manual defrost=M)

Pantry	No	-	-	-	-
Wine storage	No	-	-	-	-
Cellar	No	-	-	-	-
Fresh food	Yes	230,0	3	-	A
Chill	No	-	-	-	-
0-star or ice-making	No	-	-	-	-
1-star	No	-	-	-	-
2-star	No	-	-	-	-
3-star	No	-	-	-	-
4-star	Yes	114,0	-19	8,0	A
2-star section	No	-	-	-	-
Variable temperature compartment	-	-	-	-	-

For 4-star compartments	
Fast freeze facility	Yes
Light source parameters:	
Type of light source	LED
Energy efficiency class	G

Minimum duration of the guarantee offered by the manufacturer: 24 months

Additional information:

Weblink to the supplier's website, where the information in point 4 of Annex II of Commission Regulation (EU) 2019/2019 is found: https://www.samsung.com/support

Model placed on the Union market from 23/06/2023

EPREL registration number: 1501916

https://eprel.ec.europa.eu/qr/1501916

Supplier: SAMSUNG ELECTRONICS (UK) LIMITED (Manufacturer)

Website:

Customer care service:

Name: Public Contact

Website:

Email: eprel@samsung.com

Phone: n/a

Address:
Samsung
PO Box 12987
Blackrock
Co.Dublin
Ireland