ThinkBook 15 G5 IRL 21JD001EAU

PSREF
Product Specifications Reference

PERFORMANCE

Processor
Intel® Core™ i5-1335U, 10C (2P + 8E) / 12T, P-core 1.3 / 4.6GHz, E-core 0.9 / 3.4GHz, 12MB

Graphics
Integrated Intel Iris® Xe Graphics Functions as UHD Graphics

Chipset
Intel SoC Platform

Memory
8GB Soldered DDR4-3200

Memory Slots
One memory soldered to systemboard, one DDR4 SO-DIMM slot, dual-channel capable

Max Memory
Up to 16GB (8GB soldered + 8GB SO-DIMM) DDR4-3200 offering

Storage
256GB SSD M.2 2242 PCIe® 4.0x4 NVMe®

Storage Support
Up to two drives, 2x M.2 SSD
• M.2 2242 SSD up to 1TB
• M.2 2280 SSD up to 1TB

Storage Slot
Two M.2 2280 PCIe 4.0 x4 slots

Card Reader
4-in-1 Card Reader

Optical
None

Audio Chip
High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers
Stereo speakers, 2W x2, Dolby® Audio™

Camera
FHD 1080p with Privacy Shutter

Microphone
2x, Array

Battery
Integrated 45Wh

Max Battery Life
MobileMark® 2014: 7.6 hr (45Wh)

Power Adapter
65W USB-C® (3-pin)

DESIGN

Display
15.6" FHD (1920x1080) IPS 300nits Anti-glare, 45% NTSC

Touchscreen
None

Keyboard
Backlit, English

Case Color
Mineral Grey

Surface Treatment
Anodizing Sandblasting

Case Material
Aluminium (Top), PC-ABS (Bottom)

Dimensions (WxDxH)
357 x 235 x 18.9 mm (14.1 x 9.25 x 0.74 inches)

Weight
Starting at 1.7 kg (3.75 lbs)

SOFTWARE

Operating System
Windows® 11 Pro, English

Bundled Software
Office Trial

CONNECTIVITY

Ethernet
100/1000M (RJ-45)

WLAN + Bluetooth®
Wi-Fi® 6E, 11ax 2x2 + BT5.1

Standard Ports
- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 1x USB-C 3.2 Gen 2 (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.4)
- 1x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer, Power Delivery 3.0 and DisplayPort 1.4)
- 1x HDMI®, up to 4K/60Hz
- 1x SD card reader
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)

SECURITY & PRIVACY

Security Chip
Firmware TPM 2.0 Enabled

Fingerprint Reader
Touch Style, Integrated in Power Button

Physical Locks
Kensington® Nano Security Slot™, 2.5 x 6 mm

Other Security
Camera privacy shutter

MANAGEABILITY

System Management
Non-vPro®

SERVICE

Base Warranty
1-year, Courier or Carry-in

Included Upgrade
1Y Onsite upgrade from 1Y Courier/Carry-in (5WS0A23748)

ACCESSORIES

Bundled Accessories
None

CERTIFICATIONS

Green Certifications
- EPEAT™ Gold Registered
- ENERGY STAR® 8.0
- ErP Lot 6
- ErP Lot 26
- RoHS compliant

Other Certifications
TÜV Rheinland® Low Blue Light (Software Solution)

Mil-Spec Test
MIL-STD-810H military test passed

MODEL

TopSeller	: Yes	Announce Date	: 2023-02-24
EAN / UPC / JAN	: 196804486611	End of Support	: 2029-09-24



· Lenovo reserves the right to change specifications or other product information without notice.
· Product image on this page is a sample, it may not match the real color of this model
· Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences

Premier Support - **A direct 24x7x365 line to our most elite technicians.**

- Advanced technical support, 24x7x365, in more than 100 markets
- Technical Account Managers for proactive relationship and escalation management
- Comprehensive hardware & OEM software support
- Priority on service delivery and repair parts
- Single point of contact for simplified end-to-end case management
- Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - **Protection of your PC from the unexpected.**

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - **Included with the systems you purchase, default 1- or 3-year coverage window.**

Warranty Extensions & Upgrades - **Service and protection that's right for your circumstances.**

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.





Recommended Services

BEST	3Y Premier Support Plus upgrade from 1Y Onsite (5WS1L42349)
BETTER	3Y Premier Support Upgrade from 1Y Onsite (5WS0T36120)
GOOD	3Y Onsite upgrade from 1Y Onsite (5WS0K27114)

For a full list of accessories and services, please visit:
https://smartfind.Lenovo.com

Lenovo **PSREF**
Product Specifications Reference