MPN: RSM06U30MNWH

by Logon 10" Rack Cabinet 6U 31 x 30 SOHO Wallmount Unassembled

Product Dimensions: 312 x 300 x 300mm



They are simple and small-scale wall mount network installation solutions with low cost and robust structure. It adapts to the places where it is used with its aesthetic and decorative appearance. They have 19” and 10” width options.

Aesthetic Look
With its aesthetic and decorative appearance, it easily adapts to the places where it is used. Windshield cover; It is 4mm, smoked, antistatic, grinding, tempered and has a high break resistance, full length and locked structure.

The opening direction of the cylindrical O-lock front cover can be changed easily. The glass door module has a special u-type screw hinge system.

Variety
SOHO Cabinets have two types of width as 19” and 10”, and 2 types of depth as 400mm and 300mm.

Purpose of Usage
It is used in installation of small systems, intermediate distribution terminal, network floor distributions, wall type network installation applications.

- Cage nuts can be bought separate

Specifications

Features	**Cable entry point**	Yes
	Castor wheels	No
	Cooling type	Passive
	Frame type	Closed
	Front door construction	Glass/Steel
	International Protection (IP) code	IP20
	Key lock	Yes
	Material	Steel
	Mounting hole shape	Round
	Preassembled	No
	Product colour	White
	Rack capacity	6U
	Rack rails	Yes
	Removable side panels	No
	Soundproof	No
	Type	10" Wall Mounted Rack
Legal Information	**Country of Origin**	Türkiye
	Tariff No.	9403105800
	UNSPSC Code	24102001

Other features	**Dimensions (WxDxH)**	312x300x305 mm
Package dimensions	**Depth (package,cm)**	33 cm
	Gross Weight (Package, kg)	7.41 kg
	Height (package,cm)	35 cm
	Width (package,cm)	33 cm
Product dimensions	**Net Weight (Product, kg)**	6.68 kg
	Product Depth	30 cm
	Product Height	30 cm
	Product Width	31.2 cm
Vendor information	**Brand Name**	Lanview
	Warranty	5 Year(s)
Weight & dimensions	**Size (imperial)**	10 "

Other products in this series

Rack capacity	Black	White
6U	RSM06U30MNBL	RSM06U30MNWH
9U	RSM09U30MNBL	RSM09U30MNWH

Other images

