MPN: RAF305BL

by Logon 4 FANS, DIGITAL THERMOSTAT RACK MOUNT FAN MODULE 1U

Lanview´s 1U Horizontal cooling Unit for Superior Cooling for Network/Server Racks with an Air Flow: 560m³/hour

- 43db - 47db noise level
- Each Fan have a 2,22m3/min to 2,7m3/min suction
- BUILT-IN With C14



Specifications

Features	**Airflow**	560 m³/h
	Compatibility	19´´ mounting rail
	Compatible rack width	19 "
	Easy mounting	Yes
	Housing material	Steel
	International Protection (IP) code	IP20
	Mounting hole shape	Oval
	Number of attachment points	2
	Number of fans	4 fan(s)
	On/off switch	Yes
	Preassembled	Yes
	Product colour	Black
	Rack capacity	1U
	RoHS compliance	Yes
	Thermostat	Yes
	Type	Fan Module
Legal Information	**Country of Origin**	Türkiye
	Tariff No.	8473302000
	UNSPSC Code	43201618
Other features	**Dimensions (WxDxH)**	482x300x44 mm
	Rack mounting	Yes
	Technical features	Digital Thermostat
Package dimensions	**Gross Weight (Package, kg)**	5.31 kg
Packaging content	**Cage nuts included**	Yes

Packaging content	**Included power plug types**	EU
	Screws included	Yes
Power	**AC input frequency**	50 Hz
	Power plug type	Type F
Product dimensions	**Net Weight (Product, kg)**	5.3 kg
	Product Depth	30 cm
	Product Height	4.4 cm
	Product Width	48.2 cm
Vendor information	**Brand Name**	Lanview
	Warranty	2 Year(s)

Other images

