Poly Voyager Surround 80 UC USB-C Headset +USB-C/A Adapter



*Product image may differ from actual product

Designed for the way you work

Work where you want and sound your best with the over-ear, boomless Bluetooth® headset. Immerse yourself in rich audio, stay in complete comfort with soft ear cushions and an adjustable headband, and keep focused with adaptive ANC.

Focus with immersive audio

Engage in what's important and avoid distractions with a headset that delivers rich, clear audio for calls and music. Work where you want and sound your best with 6 built-in boomless mics plus 4 more to support adaptive ANC.

Concentrate in real comfort

You'll forget you're wearing a headset with the sleek carbon fiber design, ultra-soft ear cups, and adjustable headband for a weightless fit. Experience long-lasting comfort while you focus on work.

Engineered to work as hard as you

Maximize your productivity with the headset engineered to work as hard as you do. Stay in command of your conversations with up to 21 hours of talk time, easy on-ear controls, and smart sensors for automatic call answering.

Featuring

Get in the zone

Stay focused and keep out the distractions of the outside world with adaptive ANC and over-the-ear design.

Take your call anywhere

Sound your best where you work with 6 built-in microphones for clear transmit audio without the noise – in a boomless design.

Extended talk time

Works as long as you do with up to 21 hours of talk time or up to 24 hours of listen time.

Touch controls

Control your calls and play/pause music with easy-to-use touch controls. With just one click, you can mute yourself with a dedicated button.

Easy management via Poly Len

Take control of your deployment from anywhere via remote management with Poly Lens cloud-based device management software.

Communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.

Poly Voyager Surround 80 UC USB-C Headset +USB-C/A Adapter



*Product image may differ from actual product

Specifications

Compatibility

Compatible with PCs and smartphones via Bluetooth®, USB Type-C® BT700 adapter or USB Type-C®/A adapter
Compatible operating systems: Windows 11; Windows 10; macOS; Android™; iOS

Appearance

Product colour: Black
Ear cushions: Artificial leather (surface material)
Headphone type: Over-ear

Connectivity and communications

Wireless range: Up to 98 ft
Paired devices: Up to 2
Bluetooth version: Bluetooth® Core 5.3
Supported bluetooth profiles: A2DP; AVRCP; HFP; HSP; AVDTP
Connection type: Wireless: Bluetooth®, USB Type-C® BT700, USB Type-C®/A adapter

User interface features

Touch user controls: Volume +/-; Play/pause; Track forward/back; Programmable touch control
Button user controls: Mute; Power on/off/pairing
Indicator light: On call

Audio

Audio features:
Hybrid Active noise cancellation (ANC)
Transparency mode
Microsoft Teams Open Office certified
Acoustic protection technology: SoundGuard Digital[1,2]
Microphone type: Noise cancelling
Number of microphones: 10
Microphone bandwidth: 20 Hz to 16 kHz
Speaker bandwidth: 20 Hz to 20 kHz
Speaker size: 40 mm
Frequency response (microphone): 100 Hz to 6.8 kHz
Sensitivity (microphone): -37 dB FS
Sensitivity (speaker): 132 dB SPL

Other features

Special features: Smart sensor technology

Power specifications

Battery life: Up to 24 hours (music time); Up to 21 hours (talk time)
Battery description: Rechargeable Li-ion
Charge time: <1 hour
Battery capacity: 1100 mAh
Charging type:

Certifications

Certified collaboration software: Zoom certified; Google Meet certified

Poly Voyager Surround 80 UC USB-C Headset +USB-C/A Adapter

Specifications

Management software
Poly Lens

Weight and dimensions
Weight: 0.6 lb
Product dimensions: 7.52 x 3.03 x 7.13 in
Package weight: 0.66 lb
Package dimensions: 7.48 x 8.26 x 2.16 in

Logistic information
Master carton quantity: 5
Master carton dimension: 17.71 x 8.89 x 9.44 in
Master carton weight: 0.46 lb
Cartons per layer: 10
Layers per pallet: 7
Cartons per pallet: 70
Products per layer: 50
Products per pallet: 350
Pallet weight: 787.05 lb
Pallet dimensions: 40 x 48 x 58.66 in

Additional information
Product number: 8G7T9AA
Product name: Poly Voyager Surround 80 UC USB-C Headset +USB-C/A Adapter

Warranty
Poly standard two-year limited warranty

What is in the box
Carrying case
User guide
Wireless headset
USB charging cable
BT700 Bluetooth® Type-C® adapter
USB Type-C® to USB Type-A adapter
USB Type-C® to 3.5 mm audio cable

Poly Voyager Surround 80 UC USB-C Headset +USB-C/A Adapter

Footnotes

Messaging Footnotes

[1] Visit www.poly.com/voyager-surround-80-uc for more detail.

Technical Specifications Footnotes

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).
[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.
[3] Requires downloadable software on Poly.com/lens. Host PC requires Windows 10 or higher.

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

November 2026
us-en