Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2014 with regard to energy labelling of household washing machines and household washer-dryers

Supplier's name or trade mark: Samsung

Supplier's address: Public Contact, Samsung PO Box 12987 Blackrock Co.Dublin Ireland

Model identifier: WW90T534DAWC

General product parameters:

Parameter	Value		Parameter	Value	
Rated capacity[(a)] (kg)	9,0		Dimensions in cm	Height	85
				Width	60
				Depth	55
Energy Efficiency Index[(a)] (EEI_W)	46,7		Energy efficiency class[(a)]	A	
Washing efficiency index[(a)]	1,031		Rinsing effectiveness (g/kg)[(a)]	5,0	
Energy consumption in kWh per cycle, based on the eco 40-60 programme at a combination of full and partial loads. Actual energy consumption will depend on how the appliance is used.	0,444		Water consumption in litre per cycle, based on the eco 40-60 programme at a combination of full and partial loads. Actual water consumption will depend on how the appliance is used and on the hardness of the water.	50	
Maximum temperature inside the treated textile[(a)] (°C)	Rated capacity	28	Weighted remaining moisture content[(a)] (%)	53,9	
	Half	28			
	Quarter	23			
Spin speed[(a)] (rpm)	Rated capacity	1 400	Spin-drying efficiency class[(a)]	B	
	Half	1 400			
	Quarter	1 400			
Programme duration[(a)] (h:min)	Rated capacity	3:48	Type	Free-standing	
	Half	2:54			
	Quarter	2:44			
Airborne acoustical noise emissions in the spinning phase[(a)] (dB(A) re 1 pW)	72		Airborne acoustical noise emission class[(a)] (spinning phase)	A	

Off-mode (W) (if applicable)	0,50	Standby mode (W) (if applicable)	-
Delay start (W) (if applicable)	4,00	Networked standby (W) (if applicable)	2,00
Minimum duration of the guarantee offered by the supplier: 24 months			
This product has been designed to release silver ions during the washing cycle	**NO**		
Additional information:			
Weblink to the supplier's website, where the information in point 9 of Annex II to Commission Regulation (EU) 2019/2023 is found: https://www.samsung.com/support			

(a) for the eco 40-60 programme.

Model placed on the Union market from 03/11/2023 to 30/06/2025

EPREL registration number: 1737375

https://eprel.ec.europa.eu/qr/1737375

Supplier: SAMSUNG ELECTRONICS (UK) LIMITED (Manufacturer)

Website:

Customer care service:

Name: Public Contact

Website:

Email: eprel@samsung.com

Phone: n/a

Address:
Samsung
PO Box 12987
Blackrock
Co.Dublin
Ireland