B TECH
B-TECH AV MOUNTS

AV AWARDS 2017
MANUFACTURER OF THE YEAR
WINNER

AVAILABLE IN MULTIPLE CONFIGURATIONS

BT8333

CURVED UNIVERSAL CEILING MOUNTED MENU BOARD MOUNTING SYSTEM

Designed to mount menu boards in curved configurations, the BT8333 is a ceiling mounted system with a universal design suitable for all screens from 32" to 75". As part of B-Tech's dynamic System X range, this contemporary mounting solution is lightweight yet incredibly strong, has a high-end aesthetic quality and comes with integrated angle guides, cable management and a choice of interface arms.

SPECIFICATION

Recommended screen size	32" - 75"
Max load	50kg (per screen)
Angle adjustment range	up to +/- 45° (between screens)
VESA® & non-VESA fixings	up to 900mm*
Pole length	0.5m up to 3m (can be cut to length)
Colour (interface arms)	Black
Colour (horizontal rail)	Silver
Colour (poles & ceiling mount)	Black, White or Chrome

FEATURES

- Configurable mounting solution available to order to your requirements from stock
- Suitable for landscape or portrait mounting
- Easy to use adjustable adaptor creates an angled join between screens
- Integrated angle guides eliminate the need to measure required angles
- Integrated rail mounting guides ensure the join position is consistent throughout the installation without the need to measure
- Choose fixed or micro-adjustment interface arms
- Tool-less micro-adjustments for seamless display alignment
- All arms feature levelling screws to adjust the screen height
- Integrated cable management
- Safety screws help prevent unauthorised removal of screens
- Simple installation with all mounting hardware included

*Refers to maximum vertical fixing dimension for a typical configuration. Correctly sized interface arms and adaptors will be supplied as necessary to suit the mounting pattern you require.

75" 190CM | VESA 900 | 50KG | SYSTEM X

PER SCREEN

Angle up to +/-45° to create a concave or convex curved menu board

Choose from fixed or micro-adjustment interface arms

Integrated cable management to hide unsightly cables

Ø50mm poles are available in lengths ranging from 0.5m - 3m to provide the desired drop

TECHNICAL DRAWINGS

Example installation

DETAIL A
SCALE 1 : 4

Ø157.5mm
Ø45mm
Ø10.5mm
Ø10.5mm
127mm
13.5mm
120mm

1537.9mm
705mm
700mm
705mm
700mm
400mm
705mm
700mm
400mm
705mm
700mm
400mm

**TOP VIEW
(CEILING PLATE)**

TOP VIEW

Ø60mm
Ø50.8mm

663.1mm (MAX)
599.6mm (MAX)
479.6mm (MAX)
228mm
120mm

421.4mm

2144.6mm

SIDE VIEW

FRONT VIEW

BT8333 MOUNTING RAIL LENGTHS

BT8390-200

8.2mm
30mm
30mm
30mm

2000mm

BT8390-175

1750mm

BT8390-150

1500mm

BT8390-070

700mm

BT8390-050

500mm

BT8390-030

300mm

PACKING INFORMATION

*PLEASE NOTE, THIS IS A **MULTI-BOX** ITEM*

Colour:	Order Ref:	EAN Code:
Black / Silver	BT8333/BS	5019318301520
Chrome / Silver	BT8333/CS	5019318302435
White / Silver	BT8333/WS	5019318302442

ORIGINAL DESIGNS BY B-TECH AV MOUNTS - REGISTERED DESIGNS & PATENTS APPLY

ACCESSORIES AND RELATED PRODUCTS

BT8330

Universal Menu Board Mounting System for wall mounted menu board configurations

BT8331

Universal Pop-In, Pop-Out Menu Board System for menu board configurations

BT8332

Universal Ceiling Mounted Menu Board Mounting System configurable to suit requirements

BT8342

Universal Ceiling Mounted Video Wall System for video wall configurations