3m USB 2.0 A to B Cable - M/M

Product ID: USB2HAB3M

The USB2HAB3M 3-meter USB A-to-B cable features one USB 'A' male connector and one USB 'B' male connector, providing a high quality connection to USB 2.0 peripherals such as USB printers, scanners or external USB hard drives.

Constructed of only top quality materials and expertly designed for durability, this USB 2.0 A-B cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

• Use with any USB 2.0 rated device or add-on card

• Compatible with USB1.1 devices

• Replace worn-out or missing USB cables with this high quality cable

Features

• High quality USB 'A' and USB 'B' connectors

• Supports USB 2.0 data transfer rates up to 480 Mbps

Hardware		
	Warranty	Lifetime
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
Connector(s)		
	Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
	Connector B	1 - USB B (4 pin)
Physical Characteristics		
	Color	Black
	Wire Gauge	24/28 AWG
	Cable Length	9.8 ft [3 m]
	Product Length	9.8 ft [3.0 m]
	Product Width	0.2 in [0.5 cm]
	Product Height	0.2 in [0.5 cm]
	Weight of Product	3.7 oz [104.2 g]
Packaging Information		
	Package Quantity	1
	Package Length	6.7 in [17.0 cm]
	Package Width	5.0 in [12.8 cm]
	Package Height	0.9 in [2.4 cm]
	Shipping (Package) Weight	4.0 oz [114.0 g]
What's in the Box		
	Included in Package	1 - 3 m USB 2.0 A to B Cable - M/M
Warranty Information		
	Warranty	Lifetime

Product appearance and specifications are subject to change without notice.