Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter

Wear it well

The Blackwire 5200 Series fits your busy workday. Ergonomically designed for long lasting comfort. And with the easy-to-use connectivity you can work on a variety of devices throughout the day.

*Product image may differ from actual product

Get great sound

Tune out the inevitable workplace distractions with a headset full of features – soft, conforming ear cushions that provide passive noise canceling and a precisely tuned microphone masks nearby conversations.

Enjoy long lasting comfort

Your ears will thank you, especially after long conference calls. This headset is built to stay comfortable. Adjust it to fit the way you work. Need to move locations? The headset folds up for easy portability in the carrying case.

Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter

Featuring

Connectivity options

Enhanced connectivity for your devices: USB-C cord with tethered USB-A adapter for PC and 3.5 mm for mobile or tablet connectivity.

Comfort and durability

Ultra-soft leatherette ear cushion(s) wrapped around pillow-soft memory foam provide long lasting comfort. A lightweight cushioned metal headband offers durability and a comfortable custom fit.

Wearing style

Premium PC wideband audio with noise-cancelling microphone and Digital Signal Processing (DSP) for a more natural voice sound.

Simple call management

Use the intuitive inline controls to answer/end calls, control volume, and mute to simplify call management. Conveniently placed indicator lights provide helpful but unobtrusive user call, mute, and volume status.

SoundGuard Digital technology provides advance audio protection

Premium PC wideband audio with noise-canceling microphone and Digital Signal Processing (DSP) for a more natural voice sound.

Enhanced call quality

Dynamic EQ optimizes the quality of your voice on calls, and automatically adjusts the EQ settings when you want high-quality sound for listening to music or for multimedia playback.

Communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.

Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter

Specifications

Compatible with

Compatible operating systems: Windows 11; Windows 10; macOS; Android™; iOS

Connectivity and communications

Connection type: 3.5 mm audio; USB Type-C®; USB Type-A
Ear cushions: Artificial leather (surface material)
Headphone type: On-ear (stereo)

User interface features

Button user controls: Call answer/end; Mute; Volume +/-

Audio

Audio features:
Noise and echo reduction
Dynamic EQ optimized
Noise cancellation (NC)
Acoustic protection technology: SoundGuard Digital[1,2]
Microphone type: Omnidirectional
Microphone bandwidth: 100 Hz to 10 kHz
Speaker bandwidth: 20 Hz to 20 kHz
Speaker size: 32 mm
Signal-to-noise ratio: >24 dB
Sensitivity (microphone): 10 dB SLR
Sensitivity (speaker): 6 dB RLR

Other features

Special features: UC certified

Power supply

Impedance: 32 ohm

Certifications

Certified collaboration software: Skype for Business; Microsoft Teams; Zoom; Cisco Jabber; Works With Chromebook Certified; Avaya
Ecolabels: TCO Certified

Management

Management software:
Poly Lens
Poly Lens app (desktop)

Minimum system requirements

USB Type-A port; 3.5 mm audio; USB Type-C® port

Weight and dimensions

Product Primary Color: Black
Package Weight (metric): 300 g
Master carton quantity: 12
Master carton dimension (metric): 19.5 x 58.4 x 22.8 cm
Master carton weight (metric): 2.93 kg
Cartons per layer: 10
Pallet (layers): 6
Cartons per pallet: 60
Products per layer: 100
Products per pallet: 600
Pallet weight: ; 357 kg
Pallet dimensions (imperial):
Pallet dimensions (metric): 101.6 x 121.9 x 126.5 cm
Cable length (metric): 116 cm (inline module to headset); 94 cm (USB to inline module); 217 cm (total USB to headset)
Product number: 93S88AA
Product name: Poly Blackwire 5220 Stereo USB-C Headset +3.5mm Plug +USB-C/A Adapter

Warranty

Poly standard two-year limited warranty

Country of origin

Country of origin: Made in Mexico

What is in the box

Quick start guide
Warranty card
Carrying case
Headset
USB Type-C® to USB Type-A adapter

Technical Specifications Footnotes

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA). [2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

November 2024