AEG


9000 AutoSense Cooker Hood 60 cm

GDG966AB



Always fresh and clean kitchen air. Automatically
The 9000 AutoSense Hood, with advanced sensor technology, intuitively detects steam, grease and odours and automatically adjusts the fan power to clean the air. Cook with family and friends in a fresh kitchen with lower noise.


Product Benefits & Features



Automatically fresh and clean air with AutoSense
The AutoSense innovative sensor intuitively detects steam, grease and odours and automatically adjusts the fan power to quickly clean the air. Cook in a fresh kitchen and enjoy delicious meals together with family and friends.



Perfect Illumination – discover the magical colours of every dish
Customise kitchen experience with Perfect Illumination. Enhance your cooktop clarity with the hood light designed for cooking, or create your perfect kitchen atmosphere with adjustable warm to cool light.



SilenceTech. Maximum performance, minimum noise*
SilenceTech creates a peaceful kitchen environment where you can enjoy fresh air while cooking. The innovative technology effectively cleans your kitchen air from unwanted odours, while keeping the noise levels to a minimum.

Natural air, effortlessly and silently with the Breeze function
The Breeze function refreshes your kitchen air after cooking while quietly extracting lingering kitchen odours. Eat, relax and entertain in an enjoyable kitchen atmosphere, effortlessly and silently.

Filter cleaning notification system
The hood has a convenient filter cleaning notification system. An indicator on the hood alerts you when the grease filter and carbon filter need cleaning – there’s no need to keep track of it yourself.

- Controls
- Extraction mode
- Installation Type
- Hob²Hood function

AEG

9000 AutoSense Cooker Hood 60 cm

GDG966AB

Product Specification

Main Colour	Black/Black
Number of Speed Settings	3+Intensive, Breeze function, SilenceTech Range
Control Type	Electronic push buttons
Lamp Type	Perfect Illumination LED Stripe
Energy Rating	A++
Ducted Extraction Rate - Min/Max/Intensive (m³/h)	200/400/680
Ducted Noise Level - Min/Max/Intensive (dB)	40/54/66
Grease Filter Efficiency Rating	B
Minimum Distance from Electric Hob (cm)	50
Minimum Distance from Gas Hob (cm)	65
Annual Energy Consumption (kWh)	26.1
Size (cm)	60
Extraction Type - Recirculation	Yes
Extraction Type - Ducted	Yes
Light Temperature (k)	2700-4000-5000
Number of Lights	1
Hob2Hood Connection	Yes
Fluid Dynamic Efficiency Rating	A
Lighting Efficiency Rating	A
Min Recirculated Extraction Rate (m³/h)	140
Max Recirculated Extraction Rate (m³/h)	280
Intensive Recirculated Extraction Rate (m³/h)	385
Min Recirculated Noise Level (dB)	51
Max Recirculated Noise Level (dB)	67
PNC	942 022 759
Bar Code	7333394048741
Net Weight (Kg)	12.1
Gross Weight (Kg)	15.9
Dimensions (mm) (HxWxD)	436x542x300
Installation Type	Group
Number of Grease Filters	1
Grease Filter Type	Black design filter
Cord Length (m)	1.4
Air Outlet (mm)	150
Voltage (V)	220-240
Required Fuse (A)	No
Charcoal Filter	Included
Charcoal Filter Type	MCFB84
Long Life Filter Type	MCFB85
Super Performing Filter Type	MCFB89

PSGBCH230DE0000Z

