



An Intel® i5 OPS slot PC with Windows® 11 which supports 5K (5120x2160) resolution

This mini OPS PC with Intel® Core™ i5 inside turns your iiyama (interactive) large format display into a stand-alone solution. It comes equipped with a powerful Intel® processor with integrated Ultra HD graphics and a fast SSD drive. No hassle with cables and having to mount a PC at the back of the monitor or on a floor lift. The OPC51204BC-1 is also very quiet with a noise level below 34dB at 100% CPU load at 1 meter distance. Simply slide in the iiyama OPS slot PC and get started right away.

01 DEVICE

Type	OPS slot PC
CPU	Intel® Core™ i5-12450H (12th Gen), TPM 2.0 (Trusted Platform Module)
RAM	DDR4 3200MHz 8GB, Max. 32GB
SSD	PCIe 256GB M.2
Graphics	Integrated Intel® Iris® UHD Graphics for 12th Gen
Chipset	Intel®
Sound card	Integrated High Definition 100B Audio Stereo
Networking	10/100/1000M Adapter
WiFi	802.11 a/b/g/n/ac/ax (Wifi 6)
Bluetooth	5.2
Operating system	Windows 11 IoT Enterprise
LAN (RJ45)	x1
USB	3.0 x4, 3.2 (Type C) x1 (Not support DP Alt mode)
DisplayPort Out	x1, DP1.4 (Max resolution 3840 x 2160 60Hz)
HDMI Out	x1, HDMI2.0 (Max resolution 3840 x 2160 60Hz)
Microphone In	x1
Audio	1x Zvukový výstup

02 POWER-MANAGEMENT

Odběr energie:	80.7W typisch, 2.9W odpočinek

03 ROZMĚRY / HMOTNOST

Rozměry výrobku	180 x 119 x 30mm
Rozměry balení Š x V x D	260 x 192 x 72mm
Váha (bez balení)	0.60kg
Váha (s balením)	0.957kg
EAN code	4948570033331



04 ENVIRONMENTAL CONDITIONS

Rozsah provozní teploty	0°C - 45°C
Operation humidity	10% - 95%
Rozsah teploty v klidu	- 10°C - 50°C
Storage humidity	10% - 95%

Všechny ochranné známky jsou registrovány a chráněny. Vyhrazené právo na změny. Veškeré ploché panely LCD splňují normu ISO-9241-307:2008 v oblasti počtu vadných pixelů.

© IIYAMA CORPORATION. ALL RIGHTS RESERVED