6ft (1.8m) UK Laptop Power Cable, BS 1363 to C7, 2.5A 250V, 18AWG, Black, UK Laptop Replacement Cord, Printer Power Cable, AC Laptop Charger Cord, Laptop Power Brick Cord

Product ID: PXTNB2SUK6

This UK laptop power cord is constructed of top-quality materials, and is designed to provide a reliable power connection to your laptop or other device with a C7 power connector.

The cable is rated to carry 250V at 2.5A (H03VVH2-F 2x 0.75 mm).

Replacement C7 Power Cord

The charger cable features one UK mains plug and one IEC C7 power connector, making it a suitable replacement for a worn out or missing laptop power cable.

PXTNB2SUK6 is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility

RoHS Compliant

Applications

• Plug your laptop into a UK power outlet

• Replace worn out or missing C7 power cords

Features

• AC POWER CORD: This 6ft (1.8m) 18AWG (0.75mm2) flexible laptop power cord with BS 1363 and IEC 60320 C7 connectors is suitable for workstation/home office use Rated to carry 250V at 2.5A

• PERFORMANCE AND SAFETY: Fully molded strain relief for durability and VDE approved connectors Fire Rating: VW-1 2 Conductor Notebook Power Cable made from 100% Copper Wire

• SPECS: 6ft (1.8m) UK Computer Power Cable BS 1363 to IEC 60320 C7 18AWG (0.75mm2) 250V 2.5A (Max) Jacket Rating: H03VVH2-F Jacket Material: PVC Color: Black Temperature Range: 2 to 60 Jacket Dimensions: 3.5x6.8 mm

• COMPATIBILITY: AC Power Cord BS 1363 works with UK outlets IEC C7 connector works with most power bricks for laptops/notebooks, monitors, scanners, printers, and more Replacement laptop power supply cable/cord

• THE IT PRO'S CHOICE: Designed and built for IT Professionals, this laptop charger cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware		
	Warranty	Lifetime
	Number of Conductors	2
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Fire Rating	VW-1 Rated
Performance		
	General Specifications	Harmonized Wire Code: (H03VVH2-F 2x 0.75 mm)
Connector(s)		
	Connector A	1 - BS 1363 Power (UK)
	Connector B	1 - IEC 60320 C7 Power (Non-polarized)
Power		
	Input Voltage	250 AC
	Input Current	2.5A
Physical Characteristics		
	Color	Black
	Wire Gauge	0.75 sq mm
	Cable Length	6.0 ft [1.8 m]
	Product Length	6.0 ft [1.8 m]

	Product Width	0.5 in [1.2 cm]
	Product Height	0.4 in [1 cm]
	Weight of Product	4.9 oz [140 g]
Packaging Information		
	Package Quantity	1
	Package Length	11.4 in [29 cm]
	Package Width	8.3 in [21 cm]
	Package Height	5.7 in [14.5 cm]
	Shipping (Package) Weight	4.9 oz [140 g]
What's in the Box		
	Included in Package	power cable
Warranty Information		
	Warranty	Lifetime

Product appearance and specifications are subject to change without notice.