Tab M11 ZADA0047US

The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- MediaTek Helio G88 (8C, 2x A75 @2.0GHz + 6x A55 @1.8GHz)
- 4GB Soldered LPDDR4X
- 64GB eMMC 5.1
- Integrated Arm Mali-G52 MC2 GPU
- Android 13 or Later
- Case color - Luna Grey
- 1-year, Mail-in

Premium Care - Advanced Support from Real People. Real Fast.

REAL PERSON
Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.

REAL FAST
Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.

HASSLE FREE
'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach – that's how Premium Care delivers you the ideal support experience.

Accidental Damage Protection One - Protection for your Tablet from the unexpected.

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

Base Warranty - Included with the system you purchase with default 1-year coverage window.

Lenovo Warranty Extensions & Upgrades (up to 3 years duration) - Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service*

*Applicable in some regions only. Please check with your local services team for more details.

Recommended Accessories United Kingdom

Lenovo E310 True Wireless Stereo Earbuds (Black)

4XD1T85469

Lenovo Multi-Device Wireless Keyboard

ZG38C05805

>> View More Accessories

Product Illustration

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Tab M11 ZADA0047US

Lenovo

PERFORMANCE

Processor
MediaTek Helio G88 (8C, 2x A75 @2.0GHz + 6x A55 @1.8GHz)

Graphics
Integrated Arm Mali-G52 MC2 GPU

Chipset
MediaTek SoC Platform

Memory
4GB Soldered LPDDR4X

Storage
64GB eMMC 5.1

Card Reader
microSD Card Slot

Max Storage Support
- 64GB eMMC 5.1 on systemboard
- microSD card, supports up to 1TB (exFAT)

Speakers
4 speakers, optimized with Dolby Atmos®

Microphone
Mono

Camera
Front 8.0MP / Rear 8.0MP

VoiceCall
No

Vibration Motor
No support

Sensors
- Accelerometer (G) sensor
- Ambient light sensor (ALS)
- Gyroscope sensor
- Hall sensor

Battery
7040mAh (Typical)

Power Adapter
5V / 2A (10W)

DESIGN

Display[1]
11" WUXGA (1920x1200) IPS 400nits Anti-fingerprint, 72% NTSC, 90Hz, Touch[2]

Touchscreen
In-cell, 10-point Multi-touch

Screen-to-Body Ratio
85%

Pen
Pen Upgradable (Purchase Separately)[3]

Keyboard
None

Dimensions (WxDxH)[4]
255.26 x 166.31 x 7.15 mm (10.05 x 6.55 x 0.28 inches)

Weight[5]
Around 465 g (1.03 lbs)

Case Color
Luna Grey

Case Material
Metal

SOFTWARE

Operating System[6]
Android™ 13 or Later

CONNECTIVITY

WLAN + Bluetooth
Wi-Fi® 5, 802.11ac 1x1 + BT5.1

WWAN
WWAN Not Supported

Location Services
GPS + GLONASS + Galileo

Standard Ports
- 1x USB-C® 2.0 (support data transfer and charging)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Card slot

SERVICE

Base Warranty[7]
1-year, Mail-in

ACCESSORIES

Bundled Accessories
None

CERTIFICATIONS

Green Certifications
- ENERGY STAR® 9.0 (only available for TB330FU)
- ErP Lot 6/26
- RoHS compliant

Dust and Water Resistant
IP52

Other Certifications
TÜV Rheinland® Low Blue Light (Hardware Solution)

MODEL

Product	: TB330FU	**TopSeller**	: No
EAN / UPC / JAN	: 197532686649	**Announce Date**	: 2023-10-31

Product image is a sample, it may not match the real color of this model

Note:
[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.
[2] Measured diagonally, Lenovo Tab M11's screen size is 11" in the full rectangle without accounting for the rounded corners. Actual viewable area is less due to the rounded corners.
[3] For details upon pen compatibility, please check Here. Pen availability may vary by country / region.
[4] The system dimensions may vary depending on configurations.
[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.
[6] For latest operating system and security patches deliver plan, please visit https://support.lenovo.com/solutions/ht501098.
[7] For warranty upgrade service, please go to https://smartfind.lenovo.com/services. To learn more details of warranty policy, please access https://support.lenovo.com/warrantylookup/warrantypolicy.

- Please refer to the official Lenovo store website or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.
  · California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: https://www.calrecycle.ca.gov/Electronics/Consumer