Product information sheet - (EU) 2019/2014

Supplier's name or trade mark: HOTPOINT

Supplier's address: BEKO EUROPE MANAGEMENT S.R.L., VIA VARESINA, 204 20156 MILANO ITALY

Model identifier: NSWF 7469 GG UK

General product parameters:

<table>
<tr><th>Parameter</th><th colspan="2">Value</th><th>Parameter</th><th colspan="2">Value</th></tr>
<tr><td rowspan="3">Rated capacity (kg)</td><td colspan="2" rowspan="3">7,0</td><td rowspan="3">Dimensions in cm</td><td>Height</td><td>85</td></tr>
<tr><td>Width</td><td>60</td></tr>
<tr><td>Depth</td><td>54</td></tr>
<tr><td>Energy efficiency index (EEI_W)</td><td colspan="2">51,9</td><td>Energy efficiency class</td><td colspan="2">A</td></tr>
<tr><td>Washing efficiency index</td><td colspan="2">1,031</td><td>Rinsing effectiveness (g/kg)</td><td colspan="2">4,9</td></tr>
<tr><td>Energy consumption in kWh per cycle, based on the eco 40-60 programme at a combination of full and partial loads. Actual energy consumption will depend on how the appliance is used</td><td colspan="2">0,447</td><td>Water consumption in litre per cycle, based on the eco 40-60 programme at a combination of full and partial loads. Actual water consumption will depend on how the appliance is used and on the hardness of the water.</td><td colspan="2">45</td></tr>
<tr><td rowspan="3">Maximum temperature inside the treated textile (°C)</td><td>Rated capacity</td><td>34</td><td rowspan="3">Weighted remaining moisture content (EU 2017/1369) (%)</td><td colspan="2" rowspan="3">53,0</td></tr>
<tr><td>Half</td><td>32</td></tr>
<tr><td>Quarter</td><td>23</td></tr>
<tr><td rowspan="3">Spin speed (rpm)</td><td>Rated capacity</td><td>1351</td><td rowspan="3">Spin-drying efficiency class</td><td colspan="2" rowspan="3">B</td></tr>
<tr><td>Half</td><td>1351</td></tr>
<tr><td>Quarter</td><td>1351</td></tr>
</table>

Parameter	Value		Parameter	Value
Programme duration (h:min)	Rated capacity	3:25	Type	Free-standing
	Half	2:40		
	Quarter	2:25		
Airborne acoustical noise emissions in the spinning phase (dB(A) re 1 pW)	76		Airborne acoustical noise emission class (spinning phase)	B
Off-mode (W) (if applicable)	0,50		Standby mode (W) (if applicable)	0,50
Delay start (W) (if applicable)	4,00		Networked standby (W) (if applicable)	-

Minimum duration of the guarantee offered by the supplier: 24 months

This product has been designed to release silver ions during the washing cycle	**No**

Additional information: The years of guarantees may be different according to other national legislation. Exceptions: Ireland, United Kingdom: 12 months; Spain, Portugal: 36 months; Norway: 60 months

Weblink to the supplier's website, where the information in point 9 of Annex II to Commission Regulation (EU) 2019/2023 is found: https://docs.hotpoint.eu