8 kg Washing Machine


LFX50842B



An easy way to do laundry
Discover an effortless laundry routine with AutoSense. It adjusts washing time based on the weight and density of your load to optimise energy and water consumption, ensuring great washing results every time.

Product Benefits & Features

Effortless efficiency with every cycle
AutoSense adapts to your laundry routine. Sensors inside your washing machine measure the size of the load to optimise water and energy usage. You get great results regardless of the load's size or weight.



Faster washing with Quick Programmes
Quick Programmes adapt to your lifestyle – choose from a 60-min Wash, 30-min Wash or 14-min Refresh. A complete wash when needed, whether it's a mid-week laundry dash or for last-minute plans.

Thoroughly cleaned. With Anti-Allergy programme
The AntiAllergy Vapor 60ºC washing programme provides steam at the end of the cycle to give your clothes a hygienic and efficient clean. This helps reduce bacteria and allergens from your clothes and supports better laundry hygiene.

Quicker washes with TimeSave
Adjust your wash cycle duration with the TimeSave button. Activate and reduce in steps, trimming the wash time to the minimum you need for fast results.



Less creases with EasyIron
The EasyIron programme leaves your clothes with fewer creases. During the gentle cycle, the drum alternates the direction of its rotation, allowing clothes to move more freely. So you spend less time standing over your ironing board.

- Wool Plus Programme
- Delicate Programme
- Cottons Programmes
- Child Safety Lock
- Aqua Control
- Outdoor sports programme

AEG

8 kg Washing Machine

LFX50842B

Product Specification

Energy Rating	A
Washing Capacity (kg)	8
Max Spin Speed (rpm)	1400
Program List	Eco 40-60, Cottons, Synthetics, Delicates, Wool, Denim, Sport Wear, Spin/Drain, Rinse, Dark Clothes, Anti Allergy Vapour, 14min rapid, 30min wash, 60min wash
Push Button Functions	O/OFF, TEMP SELECTION, SPIN SELECTION, PREWASH, EXTRA RINSE, EASY IRON, DELAY, TIME SAVE, START/PAUSE
Noise Rating (dB)	B
Dimensions (mm) (HxWxD)	847x596x547
Inlet Hose Length (cm)	130
Outlet Hose Length (cm)	145
Depth Max (mm)	576
Cord Length (m)	1.8
Motor System	Permanent Magnet
Drum Volume (L)	53
Plug or Hardwired	UK Moulded Plug
Total Electricity Loading (W)	1900
Wheels/Feet	4 adjustable feet
Voltage (V)	230-240
Required Fuse (A)	13
Frequency (Hz)	50
Woolmark	None
Drawer Compartments	3
Series	5000 Series
Connectivity	No
Spin Energy Rating	B
Remaining Moisture (%)	53.4
Energy Consumption per 100 wash cycles (kWh)	47
Noise (dB)	74
Eco 40-60 Programme Duration (Hours & Minutes)	3:25
Indicators	Temperature5, ColdSpeed3, No Spin, Rinse Hold, Night, Prewash, Rinse, Easy Iron, Start/Pause
Drum Material	Stainless Steel