C HD C82 WWGD UK

12NC: F169658

GTIN (EAN) code: 8690842727887



MAIN FEATURES

Product group	Dryer
Commercial code	C HD C82 WWGD UK
GTIN (EAN) code	8690842727887
Construction type	Free-standing
Installation type	Free-standing
Removable work top	No
Loading type	Front loader
Main colour of product	White
Electrical connection rating (W)	2700
Current (A)	11,5
Voltage (V)	230-240
Frequency (Hz)	50
Length of electrical supply cord (cm)	150
Plug type	UK
Height of the product	846
Width of the product	597
Depth of the product	568
Depth with open door 90 degree (mm)	1015
Net weight (kg)	33.5

TECHNICAL FEATURES

Automatic programmes	No
Moisture monitoring system	Yes
Adjustable drying temperature	No
Progress indicator	N/A
Digital countdown indicator	Yes
Start delay options	Continuous
Start delay time max. (h)	9
Blocked filter indicator	No
Full tank indicator	Yes
Quick dry	No
Anti-crease function	Yes
Drum volume (l)	102

PERFORMANCES

Energy efficiency class - NEW (2010/30/EU)	B
Condensation efficiency class - NEW (2010/30/EU)	D
Energy consumption electric dryer, full load - NEW (2010/30/EU)	4,75
Weighted condensation efficiency	81
Weighted annual energy consumption, electric dryer - NEW (2010/30/EU)	561
Capacity cotton (kg) - NEW (2010/30/EU)	8,0
Technology	Condenser
Noise level (dB(A) re 1 pW)	66
Standard cotton programme time at full load	142
Standard cotton programme time at partial load	80
Weighted programme time	107
Power consumption in left-on mode - NEW (2010/30/EU)	1,00
Duration of the left-on mode - NEW (2010/30/EU)	30
Power consumption in off-mode - NEW (2010/30/EU)	0,50