HPKH 1261W S4UK

12NC: 869991702490

GTIN (EAN) code: 5054645702497



MAIN FEATURES

Product group	Fridge/freezer combination
Installation type	Free-standing
Type of control	Mechanical and electronic
Construction type	Free-standing
Main colour of product	New Silver – ARC 1035
Electrical connection rating (W)	130
Current (A)	1,25
Voltage (V)	220-240
Frequency (Hz)	50
Length of electrical supply cord (cm)	1.93
Plug type	UK
Total volume of the product (EU 2017/1369)	268
Star Rating	4
Height of the product	1824
Width of the product	540
Depth of the product	575
Maximum adjustability feet	0
Net weight (kg)	57

TECHNICAL FEATURES

Defrost process fridge section	Automatic
Defrost process freezer section	Automatic
Fast cooling possibility	No
Fast freezing function (EU 2017/1369)	NA
Door opened indicator freezer	No
Temperature adjustable	No
Temperature adjustable freezer	Yes
Interior ventilator fridge section	No
Number of freezing drawers	4
Number of shelves in fridge compartment	2
Material of the shelves	Glass
Number of temperature zones	2

PERFORMANCES

Energy Efficiency Class (Regulation (EU) 2017/1369)	E
Annual energy consumption in kilowatt hour per year (kWh/a) (EU) 2017/1369	246
The sum of the volumes of the chill compartments and the unfrozen compartments (EU 2017/1369)	166
The sum of the volumes of the frozen compartments (EU 2017/1369)	102
Freezing Capacity (kg/24h) (4-star Compartment) (EU2017/1369)	4,6
Climate Class (EU) 2017/1369	extended temperate/ subtropical
Airborne acoustical noise emissions (EU 2017/1369)	37
Airborne acoustical noise emission class (EU 2017/1369)	C
Frost free system	Freezer