HPKS 1262B4 UK

12NC: 869991709270

GTIN (EAN) code: 5054645709274



MAIN FEATURES

Product group	Fridge/freezer combination
Installation type	Built-in
Type of control	Mechanical and electronic
Construction type	Built-in
Main colour of product	Zinc Metal
Electrical connection rating (W)	90
Current (A)	0,5
Voltage (V)	220-240
Frequency (Hz)	50
Length of electrical supply cord (cm)	210
Plug type	UK
Total volume of the product (EU 2017/1369)	265
Star Rating	4
Height of the product	1775
Width of the product	540
Depth of the product	545
Maximum adjustability feet	0
Net weight (kg)	59.5

TECHNICAL FEATURES

Defrost process fridge section	Automatic
Defrost process freezer section	Manual
Fast cooling possibility	No
Fast freezing function (EU 2017/1369)	No
Door opened indicator freezer	No
Temperature adjustable	Yes
Temperature adjustable freezer	No
Interior ventilator fridge section	No
Number of freezing drawers	4
Number of shelves in fridge compartment	2
Material of the shelves	Glass
Number of temperature zones	2

PERFORMANCES

Energy Efficiency Class (Regulation (EU) 2017/1369)	E
Annual energy consumption in kilowatt hour per year (kWh/a) (EU) 2017/1369	230
The sum of the volumes of the chill compartments and the unfrozen compartments (EU 2017/1369)	163
The sum of the volumes of the frozen compartments (EU 2017/1369)	102
Freezing Capacity (kg/24h) (4-star Compartment) (EU2017/1369)	4,7
Climate Class (EU) 2017/1369	extended temperate/ subtropical
Airborne acoustical noise emissions (EU 2017/1369)	37
Airborne acoustical noise emission class (EU 2017/1369)	C
Frost free system	No