ThinkPad T14s Gen 6 (AMD)

PSREF
Product Specifications Reference

PERFORMANCE

Processor
AMD Ryzen™ AI 7 PRO 360 (8C / 16T, 2.0 / 5.0GHz, 8MB L2 / 16MB L3)

AI PC Category
Copilot+ PC

NPU
Integrated AMD Ryzen™ AI, up to 50 TOPS

Graphics
Integrated AMD Radeon™ 880M Graphics

Chipset
AMD SoC Platform

Memory
32GB Soldered LPDDR5x-7500

Memory Slots
Memory soldered to systemboard, no slots, dual-channel

Max Memory
32GB soldered memory, not upgradable

Storage
512GB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal 2.0

Storage Support[1]
One drive, up to 1TB M.2 2280 SSD

Storage Slot
One M.2 2280 PCIe® 4.0 x4 slot

Card Reader
None

Optical
None

Audio Chip
High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers
Stereo speakers, 2W x2, Dolby Atmos®

Camera
5.0MP + IR Discrete with Privacy Shutter

Microphone
2x, 360°

Battery
Integrated 58Wh

Power Adapter
65W USB-C® Slim (3-pin)

DESIGN

Display[2]
14" WUXGA (1920x1200) IPS 400nits Anti-glare, 100% sRGB, Low Power

Touchscreen
None

Keyboard
Backlit, English (EU)

Case Color
Black

Case Material
Carbon Fiber Hybrid (Top), Aluminium (Bottom)

Pen
Pen Not Supported

Dimensions (WxDxH)[3]
313.6 x 219.4 x 16.9 mm (12.35 x 8.64 x 0.67 inches)

Weight[4]
Starting at 1.30 kg (2.86 lbs)

SOFTWARE

Operating System
Windows® 11 Pro, WE (EN/FR/DE/NL/IT)

Bundled Software
None

CONNECTIVITY

Ethernet[5]
No Onboard Ethernet

WLAN + Bluetooth®[6]
Qualcomm® Wi-Fi® 7 NCM825, 802.11be 2x2 + BT5.3

WWAN
WWAN Upgradable to 5G

SIM Card
None

NFC
None

Standard Ports
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)

Optional Ports (configured)
- 1x Smart Card Reader
- 1x Nano-SIM Card Slot

Docking
Various docking solutions supported via Thunderbolt™ / USB-C®.
For more compatible docking solutions, please visit Docking for ThinkPad® T14s Gen 6 (AMD)

SECURITY & PRIVACY

Smart Card Reader
Smart Card Reader

Security Chip
Discrete TPM 2.0 Enabled

Fingerprint Reader
Touch Style, Match-on-Chip, Integrated in Power Button

Physical Locks
Kensington® Nano Security Slot™, 2.5 x 6 mm

Other Security
- Camera privacy shutter
- IR camera for Windows® Hello (facial recognition)
- Ultrasonic Human Presence Detection

MANAGEABILITY

System Management
Non-DASH

SERVICE

Base Warranty
3-year, Courier or Carry-in

Included Upgrade
3Y Premier Support HB (CPN), CO2 Offset 0.5 ton (2nd Generation Carbon Offset Projects)

ACCESSORIES

Bundled Accessories[7]
None

CERTIFICATIONS

Green Certifications[8]
- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant
- TCO Certified 10.0

Mil-Spec Test
MIL-STD-810H military test passed

MODEL

TopSeller	: Yes	**Announce Date**	: 2024-10-23
EAN / UPC / JAN	: 0198155012556	**End of Support**	: 2031-05-22

Note:
[1] The storage capacity supported is based on the test results with current Lenovo storage offerings.
[2] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.
[3] The system dimensions may vary depending on configurations.
[4] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.
[5] Ethernet support via optional Lenovo USB-C to Ethernet.....

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to
https://psref.lenovo.com/Detail/2579?M=21M1000MMH

Premier Support - **A direct 24x7x365 line to our most elite technicians.**

Advanced technical support, 24x7x365, in more than 100 markets

Technical Account Managers for proactive relationship and escalation management

Comprehensive hardware & OEM software support

Priority on service delivery and repair parts

Single point of contact for simplified end-to-end case management

Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - **Protection of your PC from the unexpected.**

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - **Included with the systems you purchase, default 1- or 3-year coverage window.**

Warranty Extensions & Upgrades - **Service and protection that's right for your circumstances.**

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Services

BEST	4Y Premier Support Plus upgrade from 3Y Premier Support CPN (5WS1L39249)
BETTER	4Y Premier Support upgrade from 3Y Premier Support (5WS0W86726)
GOOD	3Y Premier Support Plus upgrade from 3Y Premier Support (5WS1L39023)

For a full list of accessories and services, please visit:
https://smartfind.Lenovo.com

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

PSREF
Product Specifications Reference