Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2014 with regard to energy labelling of household washing machines and household washer-dryers

Supplier's name or trade mark: INDESIT

Supplier's address: BEKO EUROPE MANAGEMENT S.R.L., VIA VARESINA, 204 20156 MILANO ITALY

Model identifier: IDMA 75624 MY TIME UK

General product parameters:

Parameter	Value		Parameter	Value	
Rated capacity (kg)	Rated capacity[(b)]	5,0	Dimensions in cm	Height	85
	Rated washing capacity[(a)]	7,0		Width	60
				Depth	52
Energy Efficiency Index	EEI_W[(a)]	51,9	Energy efficiency class	EEI_W[(a)]	A
	EEI_{WD}[(b)]	66,9		EEI_{WD}[(b)]	D
Washing efficiency index	I_W[(a)]	1,031	Rinsing effectiveness (g/ kg dry textile)	I_R[(a)]	5,0
	J_W[(b)]	1,031		J_R[(b)]	5,0
Energy consumption in kWh per cycle, for the washing cycle of the household washer-dryer, using the eco 40-60 programme at a combination of full and partial loads. Actual energy consumption will depend on how the appliance is used		0,447	Energy consumption in kWh per cycle, for the wash and dry cycle of the household washer-dryer at a combination of full and half loads. Actual energy consumption will depend on how the appliance is used		2,659
Water consumption in litre per cycle, for the eco 40-60 programme at a combination of full and partial loads. Actual water consumption will depend on how the appliance is used and on the hardness of the water		45	Water consumption in litre per cycle, for the wash and dry cycle of the household washer-dryer at a combination of full and half loads. Actual water consumption will depend on how the appliance is used and on the hardness of the water		78

<table>
<tr><td rowspan="3">Maximum temperature inside the treated textile (°C) for the washing cycle of the household washer-dryer, using the eco 40-60 programme</td><td>Rated washing capacity</td><td>33</td><td rowspan="3">Maximum temperature inside the treated textile (°C) for the washing cycle of the household washer-dryer, using the wash and dry cycle.</td><td>Rated capacity</td><td>27</td></tr>
<tr><td>Half</td><td>27</td><td>Half</td><td>22</td></tr>
<tr><td>Quarter</td><td>22</td><td colspan="2"></td></tr>
<tr><td rowspan="3">Spin speed (rpm)[(a)]</td><td>Rated washing capacity</td><td>1 400</td><td rowspan="3">Weighted remaining moisture content (%)[(a)]</td><td colspan="2" rowspan="3">63,0</td></tr>
<tr><td>Half</td><td>1 400</td></tr>
<tr><td>Quarter</td><td>1 400</td></tr>
<tr><td rowspan="3">Eco 40-60 programme duration (h:min)</td><td>Rated washing capacity</td><td>3:27</td><td rowspan="3">Spin-drying efficiency class[(a)]</td><td colspan="2" rowspan="3">C</td></tr>
<tr><td>Half</td><td>2:41</td></tr>
<tr><td>Quarter</td><td>2:41</td></tr>
<tr><td rowspan="2">Airborne acoustical noise emissions during the spinning phase for the eco 40-60 washing cycle at rated washing capacity (dB(A) re 1 pW)</td><td colspan="2" rowspan="2">76</td><td rowspan="2">wash and dry cycle duration (h:min)</td><td>Rated capacity</td><td>7:00</td></tr>
<tr><td>Half</td><td>5:00</td></tr>
<tr><td>Type</td><td colspan="2">Free-standing</td><td>Airborne acoustical noise emission class for the spinning phase for the eco 40-60 programme at rated washing capacity</td><td colspan="2">B</td></tr>
<tr><td>Off-mode (W) (if applicable)</td><td colspan="2">0,50</td><td>Standby mode (W) (if applicable)</td><td colspan="2">0,50</td></tr>
<tr><td>Delay start (W) (if applicable)</td><td colspan="2">4,00</td><td>Networked standby (W) (if applicable)</td><td colspan="2">N/A</td></tr>
<tr><td colspan="6">Minimum duration of the guarantee offered by the supplier: 24 months</td></tr>
<tr><td colspan="3">This product has been designed to release silver ions during the washing cycle</td><td colspan="3">NO</td></tr>
<tr><td colspan="6">Additional information: The years of guarantees may be different according to other national legislation. Exceptions: Ireland, United Kingdom: 12 months; Spain, Portugal: 36 months; Norway: 60 months</td></tr>
<tr><td colspan="6">Weblink to the supplier’s website, where the information in point 9 of Annex II to Regulation (EU) 2019/2023 is found: https://docs.whirlpool.eu/</td></tr>
</table>

[(a)] for the eco 40-60 programme.

[(b)] for the wash and dry cycle.

Model placed on the Union market from 13/07/2025

EPREL registration number: 2221357

https://eprel.ec.europa.eu/qr/2221357

Supplier: BEKO EUROPE MANAGEMENT S.R.L. (Manufacturer)

Website: www.bekoeurope.com

Customer care service:

Name: BEKO EUROPE MANAGEMENT S.R.L.

Website:

Email: public_inquiry@europeanappliances.com

Phone: +39 02 83715807

Address:
VIA VARESINA, 204
20156 MILANO
ITALY