
INFORMATION

34’’ UWQHD curved monitor with USB-C dock, LAN, KVM switch and 150mm height adjustable stand



The XCB3497WQSNP is a 34-inch curved monitor that incorporates a KVM switch and a USB-C dock to simplify your workspace. The KVM switch enhances multitasking by allowing you to control multiple computers from a single monitor, keyboard, and mouse. The USB-C dock reduces cable clutter and simplifies connectivity even further, allowing a single cable to carry video, data, and power to charge your notebook. Additionally, when the monitor is connected to a LAN network, your notebook automatically gains network access. The VA panel technology delivers high contrast and deep black levels and wide viewing angles for consistent image quality regardless of your position for a richer and more vivid viewing experience.

For optimal comfort, the 15cm height-adjustable stand allows you to customize the screen position, while the Flicker-Free panel and Blue Light reduction function help minimize eye strain.



Snadné ovládání více zařízení pomocí KVM

Easily switch between multiple computers using one monitor, keyboard, and mouse, making multitasking smooth and efficient.




USB-C dok: pořádek & snadné připojení

Connect everything with just one cable — handle video, data, and power while keeping your desk clean and organized.



Zakřivený pro pohlcující zážitek ze sledování

Step into an immersive, natural viewing setup that minimizes distortion and reduces eye strain during long work or entertainment sessions.



Multitasking s ultraširokým QHD

Get more space to multitask, compare documents side by side, or fully immerse in your content without switching windows.

SPECIFICATION

01 CHARAKTERISTIKA OBRAZU

Design	curved
Úhlopříčka monitoru	34", 86.7cm
Panel	VA panel, matte finish
Zakřivení	1500R
Nativní rozlišení	3440 x 1440 @120Hz (4.9 megapixel UWQHD, DisplayPort & USB-C)
Formát obrazu	21:9
Jas	350 cd/m²
Kontrast	3000:1
Pokročilý kontrast	80M:1
Čas rekace (MPRT)	0.4ms
Úhel sledování	horizontální/vertikální: 178°/178°, na parvo/na lefo: 89°/89°, nahoru/dolů: 89°/89°
Barevná podpora	16.7mln (sRGB: 99%; NTSC: 93%)
Horizontalfrequenz	30 - 180kHz
Arbeitsfläche H x B	797.2 x 333.7mm, 31.3 x 13.1"
Velikost bodů	0.232mm
Barva rámu	matná, černá

02 ROZHRANÍ / KONEKTORY / OVLÁDÁNÍ

Vstupní porty	HDMI x2 (1x v.2.0 and 1x v. 1.4, 3440x1440 @100Hz, 2560x1440 @120Hz) DisplayPort x1 (v.1.4, 3440 x 1440@ 120Hz) USB-C x1 (3440 x 1440@ 120Hz, PD 95W)
USB HUB	x4 (2x Type A v.3.2 Gen 1 (5Gbps, 4.5W) 2x Type C (5Gbps, 7.5W))
USB-C DOCK	x1 (Power delivery 95W, LAN, USB v. 3.2 (Gen 1, 5Gbit))
HDCP	ano
Konektor pro sluchátka	ano
RJ45 (LAN)	x1

03 VLASTNOSTI

KVM switch	ano
Redukce modrého světla	ano
Flicker Free LED	ano
Adaptive Sync support	FreeSync Premium, HDMI: 2560 x 1440 @48-100Hz, DP / USB-C: 3440 x 1440 @48-120Hz
Extra	i-Style Colour
Jazyky OSD	EN, DE, FR, ES, IT, RU, JP, CZ, NL, PL
Kontrolní tlačítka	Joystick: Power/Menu (Centre), Forward/Signal Select, Backward, Left/i-Style colour/ECO/BlueLight Reducer, Right/Volume

Nastavitelné parametry	picture adjust (brightness, contrast, Eco, ACR, OD, AdaptiveSync, motion blur reduction, X-Res technology, black tuner), colour settings (6-axis, i-Style colour, blue light reducer, gamma, RGB range, colour temp.,), OSD (OSD H. position, OSD V. position, OSD time, OSD background, DDC/CI control, display information), language, miscellaneous (sharpness, video mode adjust, opening logo, power LED, Mac address, USB charge, USB C speed), KVM (HDMI1, HDMI2, DisplayPort, USB C), input select, audio settings (volume, mute audio), recall
Reproduktory	2 x 5W
Výhoda	Kensington-lock™ připraven, DDC2B

04 MECHANICKÉ ČÁSTI

Úpravy polohy	swivel, náklon
Výškově nastavitelné	150mm
Úhel otočení	90°; 45° na lefo; 45° na parvo
Úhel náklonu	23° nahoru; 5° dolů
VESA	100 x 100mm
Systém správy kabelů	ano

05 ZAHRNUTÉ PŘÍSLUŠENSTVÍ

Kabely	napájecí, USB, HDMI, DP, USB-C
Ostatní	uživatelský manuál, instrukce bezpečnosti

06 POWER-MANAGEMENT


Napájecí zdroj:	interní
Napájení	AC 100 - 240V, 50/60Hz
Odběr energie	32W default , 0.5W odpočinek, 0.3W vypnutý
Odběr energie:	0.5W odpočinek

07 UDRŽITELNOST

Předpisy	TCO Certified, CE, TÜV-GS, EAC, VCCI-B, PSE, RoHS support, ErP, WEEE, REACH, UKCA
Energetická třída (Regulation (EU) 2017/1369)	F
EPEAT Silver	*registration varies by country, go to www.epeat.net for details

08 ROZMĚRY / HMOTNOST

Rozměry výrobku Š x V x D	807 x 426 (576) x 245.5mm
Rozměry balení Š x V x D	928 x 480 x 186mm
Váha (bez balení)	9.7kg
Váha (s balením)	14.1kg
EAN code	4948570125142


297.0
245.5
807.0
175.0
365.0
110.0
428.0
426.0 (576.0)
239.5
4xM4 SCREW HOLE
(VESA MOUNT)
100.0
100.0
50.5
45.0

GALERIE


iiyama
ProLite
XCB3497WQSNP
34"
86.4cm
VA
3440x1440
CURVED
1500R
95W
USB-C
KVM
SWITCH
15cm
5 YEAR WARRANTY


iiyama
ProLite
XCB3497WQSNP
34"
86.4cm
VA
3440x1440
CURVED
1500R
95W
USB-C
KVM
SWITCH
15cm


iiyama
ProLite
XCB3497WQSNP
34"
86.4cm
VA
3440x1440
CURVED
1500R
95W
USB-C
KVM
SWITCH
15cm
5 YEAR WARRANTY


iiyama
ProLite
XCB3497WQSNP
34"
86.4cm
VA
3440x1440
CURVED
1500R
95W
USB-C
KVM
SWITCH
15cm


iiyama
ProLite
XCB3497WQSNP
34"
86.4cm
VA
3440x1440
CURVED
1500R
95W
USB-C
KVM
SWITCH
15cm





Všechny ochranné známky jsou registrovány a chráněny. Vyhrazené právo na změny. Veškeré ploché panely LCD splňují normu ISO-9241-307:2008 v oblasti počtu vadných pixelů. **© IIYAMA CORPORATION. ALL RIGHTS RESERVED**