AEG

8000 AuroraTech Cooker Hood 60 cm

NDV8761CB



The smart hood with adaptive lighting
The 8000 AuroraTech® Hood introduces smart lighting to your kitchen. It automatically adapts the illumination colour and intensity based on the time of day, creating the perfect ambiance. Use the app for the smart lighting experience.

Product Benefits & Features



AuroraTech®. Transform your kitchen with adaptive light
AuroraTech® automatically adapts the colour and intensity of your cooker hood's light according to the time of day to create the perfect kitchen ambience and enhance your comfort. Use the app for the smart illumination experience.



SilenceTech. Maximum performance, minimum noise
SilenceTech creates a peaceful kitchen environment where you can enjoy fresh air while cooking. The innovative technology effectively cleans your kitchen air from unwanted odours, while keeping the noise levels to a minimum.



Natural air, effortlessly and silently with the Breeze function
The Breeze function refreshes your kitchen air after cooking while quietly extracting lingering kitchen odours. Eat, relax and entertain in an enjoyable kitchen atmosphere, effortlessly and silently.



Hob2Hood®. The perfect partner when you cook.
The Hob2Hood® function wirelessly activates the hood lights when you turn on the hob. When you start cooking, the fan speed is regulated based on the heat settings on the hob. Cook delicious meals without worrying about odours and vapours.



ExtractionTech Pro cooker hood: High power, exceptional freshness
Experience superior kitchen air quality with the ExtractionTech Pro cooker hood. Equipped with our most powerful motor and intensive speed option, it efficiently extracts cooking vapours ensuring an exceptionally fresh cooking environment.

- Control type: Electronic touch controls with 3+2 Intensive; Breeze function; SilenceTech Range speeds.
- Aluminium grease filters
- Extraction mode
- Recirculation mode
- Hob2Hood®: Allows you to control the cooker hood via your hob.
- Grease filter indicator.
- Charcoal filter indicator.
- Grease filter type and number: Black Aluminium mesh, 2

AEG

8000 AuroraTech Cooker Hood 60 cm

NDV8761CB

Product Specification

Main Colour	Black
Number of Speed Settings	3+2 Intensive; Breeze function; SilenceTech Range
Control Type	Touch on glass
Lamp Type	AuroraTech; Rectangular led
Energy Rating	A+
Ducted Extraction Rate - Min/Max/Intensive (m³/h)	260/445/760
Ducted Noise Level - Min/Max/Intensive (dB)	43/55/67
Grease Filter Efficiency Rating	B
Minimum Distance from Electric Hob (cm)	50
Minimum Distance from Gas Hob (cm)	65
Annual Energy Consumption (kWh)	42.9
Size (cm)	60
Extraction Type - Recirculation	Yes
Extraction Type - Ducted (External)	Yes
Light temperature, K	2700-4000-5000
Number of Lights	2
Hob2Hood Connection	Yes
Fluid Dynamic Efficiency Rating	A
Lighting Efficiency Rating	A
Min Recirculated Extraction Rate (m³/h)	250

Max Recirculated Extraction Rate (m³/h)	440
Intensive Recirculated Extraction Rate (m³/h)	725
Min Recirculated Noise Level (dB)	51
Max Recirculated Noise Level (dB)	71
PNC	942 051 564
Bar Code	7333394077635
Net Weight	16.6
Gross Weight (Kg)	22.5
Dimensions (mm) (HxWxD)	1260x598x410
Installation Type	Chimney
Number of Grease Filters	2
Grease Filter Type	Black Aluminium mesh
Cord Length (m)	1.1
Air Outlet (mm)	150
Voltage (V)	220-240
Required Fuse (A)	No
Charcoal Filter	2; Accessory
Charcoal Filter Type	MCFB91
Long Life Filter Type	MCFB92
Super Performing Filter Type	MCFB93

