9000 Touch Sure Gas On Glass Hob 80cm

HVB8453IB





Perfect contol of the flame effortlessly with Touchsure
Intuitive Touchsure controls give you full control of the flame. Adjust the heat up and down precisely for perfect cooking results. With no buttons to trap cooking spills, clean up is effortless.

Product Benefits & Features



IGNITE. SEAR. CONTROL. WITH ABSOLUTE ASSURANCE
The advanced TouchSure hob from AEG comes with a range of reassuring safety features that provide absolute confidence in – and absolute command over – gas cooking. It's a traditional method harnessed with our responsive technology. Instilling confidence to turn up the heat.



Hob2Hood. The hands-free hood
Hob2Hood automatically controls your cooker hood's power level and lights while you concentrate on the key moments of getting your dish just right.



STAY INFORMED. INSTANTLY
The FlameLight LED Indicators clearly display whether the flame is on or off while Residual Heat Indicators identify if the pan supports are still hot after use.



Automatic Switch-Off for peace of mind
Automatc Switch-Off automatically turns off the hob if it senses that the flame has been left on for an unsually long period. Give yourself more peace of mind in the kitchen.



Minute Minder. Keeps track of your cooking
The hob comes complete with a convenient Minute Minder, allowing you to monitor the progress of your cooking and always stay in absolute control of the food you're creating.

- Hob2Hood®: Allows you to control the cooker hood via your hob.
- OptiFix™: Only one step to install the hob.
- Child lock safety function.
- Gas on Glass
- Stop & Go function
- Residual Heat Indicators
- Minute Minder
- Cast Iron Pan Supports

9000 Touch Sure Gas On Glass Hob 80cm

HVB8453IB

Product Specification

Series	9000	Wok burner	No
Main Colour	Black		
Plug or Hardwired	Hardwired connection only		
Dimensions (mm) (WxD)	800x520		
Built-in Dimensions (mm) (HxWxD)	49x755x490		
Cord Length (m)	1.1		
LED Colour	Red		
Middle - Power/Diameter	1800W/80mm		
Right Front - Power/Diameter	1000W/65mm		
Left Middle - Power/Diameter	3500W/128mm		
Right Rear - Power/Diameter	1800W/80mm		
Control Type	Hawk		
Gas Supply: Natural Gas	G20 (2H) 20 mbar		
Gas Replacement	G30/G31 (3+) 28-30/37 mbar; With Additional Injectors		
Product Number (PNC)	All Open		
Pan Support Type	4, Cast Iron		
Number of Cooking Zones	4		
Max Power Gas (W)	8200		
Hob Type	Gas On Glass Hob		
Frame Type	Statement Frame Matt Black		
Hob Safety	Automatic Switch Off, Child-lock, Thermocouple		
Net Weight (Kg)	15.1		
Gross Weight (Kg)	17.4		

