C HSD 82M BB UK

12NC: F171937

GTIN (EAN) code: 5054645719372



MAIN FEATURES

Product group	Dryer
Commercial code	C HSD 82M BB UK
GTIN (EAN) code	5054645719372
Construction type	Free-standing
Installation type	Free-standing
Removable work top	N/A
Loading type	Front loader
Main colour of product	Black
Electrical connection rating (W)	900
Current (A)	4
Voltage (V)	230-240
Frequency (Hz)	50
Length of electrical supply cord (cm)	150
Plug type	UK
Height of the product	846
Width of the product	598
Depth of the product	545
Depth with open door 90 degree (mm)	1040
Net weight (kg)	39.5

TECHNICAL FEATURES

Automatic programmes	No
Moisture monitoring system	Yes
Adjustable drying temperature	No
Progress indicator	Yes
Digital countdown indicator	Yes
Start delay options	Continuous
Start delay time max. (h)	24
Blocked filter indicator	Yes
Full tank indicator	Yes
Quick dry	No
Anti-crease function	Yes
Drum volume (l)	93

PERFORMANCES

Energy efficiency class - NEW (2010/30/EU)	A+
Condensation efficiency class - NEW (2010/30/EU)	C
Energy consumption electric dryer, full load - NEW (2010/30/EU)	2,18
Weighted condensation efficiency	82
Weighted annual energy consumption, electric dryer - NEW (2010/30/EU)	265
Capacity cotton (kg) - NEW (2010/30/EU)	8,0
Technology	Heat Pump
Noise level (dB(A) re 1 pW)	64
Standard cotton programme time at full load	209
Standard cotton programme time at partial load	125
Weighted programme time	161
Power consumption in left-on mode - NEW (2010/30/EU)	1,00
Duration of the left-on mode - NEW (2010/30/EU)	30
Power consumption in off-mode - NEW (2010/30/EU)	0,50