ThinkStation P3 Tower 30GS00HWUS

The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- Intel Core i5-14500, 14C (6P + 8E) / 20T, P-core 2.6 / 5.0GHz, E-core 1.9 / 3.7GHz, 24MB Intel Smart Cache
- 2x 32GB UDIMM DDR5-4400 Non-ECC
- 1x 2TB SSD M.2 2280 PCIe 4.0x4 Performance NVMe Opal
- Integrated Intel UHD Graphics 770 + 1x NVIDIA RTX 2000 Ada Generation 16GB
- Windows 11 Pro, English
- 3Y Premier Support Upgrade from 3Y Onsite

Premier Support - A direct 24x7x365 line to our most elite technicians.

- Advanced technical support, 24x7x365, in more than 100 markets
- Technical Account Managers for proactive relationship and escalation management
- Comprehensive hardware & OEM software support
- Priority on service delivery and repair parts
- Single point of contact for simplified end-to-end case management
- Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Accessories United Kingdom

Lenovo Wired VoIP Headset (Teams)

4XD1M45626

ThinkPad Bluetooth Presenter Mouse (Aura Edition)

4Y51T62792

Lenovo 310 FHD Webcam Black

GXC1S15024

NVIDIA T1000 8GB 4xmDP Graphics Card Bulk Pack (40 orders per pack)

4X61R69220



Lenovo 4TB Performance PCIe Gen4 NVMe OPAL M.2 2280 SSD

4XB1Q31359

ThinkStation Intel Wi-Fi AX211 WLAN Module - P3

4XH1N92877

>> View More Accessories

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

ThinkStation P3 Tower 30GS00HWUS

Lenovo

PERFORMANCE

Processor
Intel Core™ i5-14500, 14C (6P + 8E) / 20T, P-core 2.6 / 5.0GHz, E-core 1.9 / 3.7GHz, 24MB Intel® Smart Cache

AI PC Category[1]
AI-Ready Workstations

Processor Sockets
1x FCLGA1700

Integrated Graphics
Integrated Intel® UHD Graphics 770

Discrete Graphics
1x NVIDIA® RTX 2000 Ada Generation 16GB

Chipset
Intel® W680 Chipset

Memory[2]
2x 32GB UDIMM DDR5-4400 Non-ECC

Memory Slots
4 DDR5 DIMM slots, 2 channels capable

Max Memory[3]
Up to 128GB (4x 32GB DDR5 UDIMM)

PCIe NVMe Controller
Integrated NVMe® Controller

PCIe NVMe Drive
1x 2TB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal

SATA Controller
Onboard Intel® RSTe SATA RAID

SATA/SAS Drive
None

Optical
None

Audio Chip
High Definition (HD) Audio, Realtek® ALC897Q-CG codec

Power Supply
1100W Platinum Fixed

DESIGN

Keyboard
USB Traditional Keyboard, Black, English

Mouse
USB Calliope Mouse, Black

Dimensions (WxDxH)[4]
180 x 370 x 415 mm (7.09 x 14.57 x 16.34 inches)

Weight[5]
13.61 kg (30.00 lbs, maximum configuration)

CONNECTIVITY

Onboard Ethernet
Intel® I219-LM, 1x GbE RJ-45

Optional Ethernet
None

WLAN + Bluetooth
Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3, vPro®

Card Reader
SD Card Reader

Front Ports
- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), data transfer only
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 1x headphone / microphone combo jack (3.5mm)
- 1x microphone (3.5mm)

Optional Front Ports (configured)
1x SD card reader

Rear Ports
- 4x USB-A (USB 5Gbps / USB 3.2 Gen 1), one supports Smart Power On
- 1x HDMI® 2.1 TMDS
- 2x DisplayPort™ 1.4
- 1x Ethernet (GbE RJ-45)
- 1x line-out (3.5mm)

Optional Rear Ports (configured)
2x PS/2

SECURITY & PRIVACY

Security Chip
Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Physical Locks
- Kensington Security Slot™, 3 x 7 mm
- Padlock Loop

Cover Lock
None

Cable Lock
No Cable

Chassis Intrusion Switch
None

MANAGEABILITY

System Management[6]
Intel® vPro® Enterprise with Intel® AMT 16

SERVICE

Base Warranty
3-year, Onsite

Included Upgrade
3Y Premier Support Upgrade from 3Y Onsite

CERTIFICATIONS

ISV Certifications
Please visit ISV certifications for Lenovo® Workstations

SOFTWARE

Operating System
Windows® 11 Pro, English

Bundled Software
None

MODEL

TopSeller	: Yes	EAN / UPC / JAN	: 198158609647
Announce Date	: 2025-04-15	End of Support	: 2031-01-31

Product image is a sample, it may not match the real color of this model

Note:
[1] With scalable configurations of higher-performance CPUs and professional NVIDIA RTX GPUs, in addition to advantage of the same modern AI PC technology, AI-Ready workstation power the demanding AI consumption & development workflows.
[2] 4400 MT/s is maximum operating speed, memory operating speed varies depending on memory configuration: 1x 8GB / 2x 8GB / 1x 16GB / 2x 16GB / 2x 32GB configurations run at 4400 MT/s; 4x 8GB / 4x 16GB configurations run at 4000 MT/s; 4x 32GB configuration runs at 3600 MT/s.
[3] The max memory is based on the test results with current Lenovo memory offerings.
[4] The system dimensions may vary depending on configurations.
[5] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.
[6] Intel vPro offers a superset of DASH's defined capabilities.

- Please refer to the official Lenovo store website or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.