Specifications

Eaton SMART1500RM2ULN

SmartPro 1500VA 1440W 120V Line-Interactive Sine Wave UPS - 8 Outlets, Preinstalled WEBCARDLXE Network Interface, 2U Rack/Tower

General specifications

PRODUCT NAME	Eaton Tripp Lite series SmartPro UPS
CATALOG NUMBER	SMART1500RM2ULN
UPC	037332297648
PRODUCT LENGTH/DEPTH	19.27 in
PRODUCT HEIGHT	3.43 in
PRODUCT WIDTH	17.3 in
PRODUCT WEIGHT	41.78 lb
WARRANTY	5 year limited
COMPLIANCES	FCC Class B RoHS
CERTIFICATIONS	CSA certified UL 1778
GLOBAL CATALOG	SMART1500RM2ULN
PRODUCT TYPE	UPS

Powering Business Worldwide

Battery

AC SUPPRESSION JOULE RATING	570
BATTERY TYPE	Lithium-ion
RUNTIME AT FULL LOAD	7.1 min. (1440W)
RUNTIME AT HALF LOAD	15.4 min

Electrical output

TOPOLOGY	Line-interactive
OUTPUT POWER FACTOR	0.96
NOMINAL OUTPUT VOLTAGE	110V 115V 120V
ELECTRIC CURRENT - MAX	• 12A • 12
LOAD MANAGEMENT RECEPTACLES	Two switchable single-outlet load banks
OUTPUT CAPACITY (WATTS)	1440

Electrical input

INPUT NOMINAL VOLTAGE	120 VAC
NOMINAL INPUT VOLTAGE SUPPORTED	120 VAC
UPS INPUT CONNECTION TYPE	5-15P

Environmental

RELATIVE HUMIDITY	0-95% non-condensing

Additional specifications

FORM FACTOR	Rackmount Tower Wall-mount
RACK SIZE	2U
PACKAGE CONTENTS	• 1500VA 1440W 120V Line-Interactive UPS • WEBCARDLXE network interface • USB cable • DB9 cable • EPO cable • Rack-mounting hardware • Owner's manual
PHASE (INPUT)	Single-phase

Resources

BROCHURES	Eaton Single Phase UPS Lithium-ion Solutions brochure

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.