Yoga Pro 7 14IAH10 83KF0002FR

Lenovo

PSREF
Product Specifications Reference

PERFORMANCE

Processor
Intel® Core™ Ultra 9 285H, 16C (6P + 8E + 2LPE) / 16T, Max Turbo up to 5.4GHz, 24MB

AI PC Category[1]
AI PC

NPU
Integrated Intel® AI Boost, up to 13 TOPS

Graphics
Integrated Intel® Arc™ 140T GPU

Chipset
Intel® SoC Platform

Memory
32GB Soldered LPDDR5x-8533

Memory Slots
Memory soldered to systemboard, no slots, dual-channel

Max Memory
32GB soldered memory, not upgradable

Storage
1TB SSD M.2 2242 PCIe® 4.0x4 NVMe®

Storage Support[2][3]
Up to two drives, 2x M.2 SSD
• M.2 2242 SSD up to 1TB

Storage Slot
Two M.2 slots
• One M.2 2242 PCIe® 4.0 x4 slot
• One M.2 2280 PCIe® 4.0 x4 slot

Card Reader
SD Card Reader

Audio Chip
High Definition (HD) Audio, Realtek® ALC3306 codec

Speakers
4 stereo speakers, 2W x2 (woofers), 2W x2 (tweeters), optimized with Dolby Atmos®, Smart Amplifier (AMP)

Camera
5.0MP + IR with E-shutter

Microphone
4x, Array

Battery
84Wh

Power Adapter
100W USB-C® Slim (3-pin)

DESIGN

Display
14.5″ 3K (3000x1876) OLED 1000nits (peak) / 500nits (typical) Glossy / Anti-fingerprint, 100% DCI-P3, 120Hz, Eyesafe®, Dolby Vision®, DisplayHDR™ True Black 1000, Glass, Touch, X-Rite®, PureSight Pro

Touchscreen
On-cell, 10-point Multi-touch

Color Calibration
Factory Color Calibration

Keyboard
Backlit, French

Touchpad
Buttonless glass surface multi-touch touchpad, supports Precision TouchPad (PTP), 80 x 135 mm (3.15 x 5.31 inches)

Case Color
Luna Grey

Surface Treatment
Aluminium Stamping (Anodized with Sandblasting)

Case Material
Aluminium (Top), Aluminium (Bottom)

Pen
None

Dimensions (WxDxH)[4]
325.3 x 228.1 x 16.9 mm (12.81 x 8.98 x 0.67 inches)

Weight[5]
Starting at 1.54 kg (3.39 lbs)

SOFTWARE

Operating System
Windows® 11 Home, French

Bundled Software
Office Trial

CONNECTIVITY

WLAN + Bluetooth®[6]
Wi-Fi® 7, 802.11be 2x2 + BT5.4

WWAN
Non-WWAN

Ethernet
No Onboard Ethernet

Standard Ports[7]
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1), Always On
- 2x USB-C® (Thunderbolt™ 4 / USB4® 40Gbps), with USB PD 3.0 and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 8K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x SD card reader

Docking
Various docking solutions are supported via Thunderbolt™. For more compatible docking solutions, please visit Docking for Yoga® Pro 7 14IAH10

SECURITY & PRIVACY

Security Chip
Firmware TPM 2.0

Fingerprint Reader
None

Other Security
- E-shutter
- IR camera for Windows® Hello (facial recognition)

SERVICE

Base Warranty
2-year, Courier or Carry-in

Included Upgrade
None

ACCESSORIES

Bundled Accessories
None

CERTIFICATIONS

Green Certifications[8]
- Carbon Neutral Certified
- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 6/26
- RoHS compliant

Other Certifications
- Intel® Evo™ Platform
- Eyesafe® Certified 2.0
- TÜV Rheinland® Flicker Free
- TÜV Rheinland® Low Blue Light (Hardware Solution)

Mil-Spec Test
MIL-STD-810H military test passed (21 test items)

MODEL

TopSeller	: No	**Announce Date**	: 2025-03-03
EAN / UPC / JAN	: 198155851193	**End of Support**	: 2031-04-03

Note:
[1] AI PCs have a NPU capable of 10+ TOPs to run the Copilot assistant by pressing the optional Microsoft Copilot key or using Win + C.
[2] The storage capacity supported is based on the test results with current Lenovo storage offerings.
[3] The system supports dual SSD via two M.2 slots, but.....

· Lenovo reserves the right to change specifications without notice.

To see more note information, please link to
https://psref.lenovo.com/Detail/2652?M=83KF0002FR

Premium Care - **Advanced Support from Real People. Real Fast.**

REAL PERSON
Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

REAL FAST
Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

HASSLE FREE
'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

PC HEALTH CHECK
Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - **Protection of your PC from the unexpected.**

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – **Included with the systems you purchase, default 1- or 3-year coverage window.**

Warranty Extensions & Upgrades – **Service and protection that's right for your circumstances.**

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories

Lenovo Professional Wireless Combo Keyboard & Mouse (US English)
4X30H56796
This sleek and stylish full-size keyboard and mouse combo offers exceptional quality in a modern wireless solution. The slim 3-zone keyboard with number pad has responsive quiet keys and a premium typing experience. O...

Lenovo Essential USB Mouse
4Y50R20863
The Lenovo Essential USB Mouse is more than your basic mouse. It features an easy plug-and-play connection to PCs with USB cord. The ergonomic full-size design provides comfortable grip for all day comfort. A high-re...

For a full list of accessories and services, please visit:
https://smartfind.Lenovo.com

Lenovo **PSREF**
Product Specifications Reference