HP Poly Studio A2 Black Table Microphone w/ Mounting Plate I/O cables

*Product image may differ from actual product

Bring exceptional clarity to the table

Make audio come alive in every meeting with a simple, scalable, cost-efficient table microphone. Effortlessly expand audio coverage and enable distraction-free communication while seamlessly scaling and deploying.

No distractions. Just clear conversation

Hear everything that matters and prioritize the conversation so remote participants receive high-quality sound.

Amplify coverage, just like that

Daisy chain up to 8 HP Poly Studio A2 Table Microphones[1] seamlessly - no complex setups required.

Purposefully designed

Elevate the appearance of any conference table with a compact design, unmatched cable management and versatile mounting and color options.

Featuring

Precise audio capture

Capture speech without distractions with this multi-directional microphone that ensures all in-room participants are heard equally.

Unmatched clarity

Get conversational sound that is crystal-clear with expanded audio pick up enhanced by Poly AI-powered audio innovations.

Scale up with ease

Simply daisy chain up to 8 HP Poly Studio A2 Table Microphones for optimal room coverage and easily reconfigure as your needs change.

Cabling done right

Get an immaculate setup with discreet cable management for tabletop installation. Neatly position your device with the included magnetic mount.

Clean setup, always

With versatile installation options, streamline or completely hide cable presence. Get a clean set-up that perfectly blends with any room aesthetics.

Elegant and compact design

Revamp any conference table with an elegant design, a compact and purposeful form factor available in black.

Sustainability in action

Designed with purpose

Containing at least 60% recycled plastics[2] and shipped in paper-based packaging[3], this table microphone enables more impactful meetings with less impact on the environment.

HP Poly Studio A2 Black Table Microphone w/ Mounting Plate I/O cables

*Product image may differ from actual product

Specifications

Compatibility

Compatible with: Poly Studio G62: up to 8 Studio A2 table microphones; Poly Studio X72 & V72: up to 4 Studio A2 table microphones; Poly Studio X52 & V52: up to 4 Studio A2 table microphones; Poly Studio X32: up to 2 Studio A2 table microphones; Poly Studio V12: only 1 Studio A2 table microphone[1].

Appearance

Product colour: Black
Cable length: 6 m

Connectivity and communications

External I/O ports:
3-pin JST output; 4-pin JST input

Audio

Microphone type: Four uni-directional cardioid microphone elements
Microphone Pickup Range: Up to 1.8 m radius (Poly Noise Block AI off); Up to 4.3 m radius (Poly Noise Block AI on) Up to 6 ft radius (Poly Noise Block AI off); Up to 14 ft radius (Poly Noise Block AI on)
Signal-to-noise ratio: >68 dBA
Frequency response (microphone): 100 Hz to 20 kHz
Sensitivity (microphone): -35 dB (V/Pa) at 1 kHz

Other features

Special features: Digital transport (up to 18 m between devices); Supports daisy-chain capability of up to 8 A2 table mics; Built on A2B technology

Power specifications

Operating voltage: 2 W

Environmental

Operating altitude: 3,048 m
Operating humidity range: 15 to 80%
Non-operating humidity range: 5 to 95%
Operating temperature range: 0 to 40°C
Non-operating temperature: -40 to 70 °C -40 to 158 °F
Sustainable impact specifications: Contains at least 60% recycled plastic content; Paper-based packaging[2,3]

HP Poly Studio A2 Black Table Microphone w/ Mounting Plate I/O cables

*Product image may differ from actual product

Specifications

Management software
Poly Lens

Weight and dimensions
Weight: 120 g
Product dimensions: 92 x 92 x 24 mm
Package weight: 470 g
Package dimensions: 168 x 140 x 67 mm

Logistic information
Master carton quantity: 12
Master carton dimension: 43.5 x 29 x 19 cm
Master carton weight: 6.4 kg
Cartons per layer: 8
Layers per pallet: 7 (air); 10 (ocean)
Cartons per pallet: 56 (air); 80 (ocean)
Products per layer: 96
Products per pallet: 672 (air); 960 (ocean)
Pallet weight: 373.8 kg
Pallet dimensions: 120 x 100 x 203.3 cm (ocean); 120 x 100 x 146.3 cm (air)

Additional information
UPC number: (AB1) 199642005501; (ABT) 198828502711; (AC3) 198828502728
Product number: B22X6AA
Product name: HP Poly Studio A2 Black Table Microphone w/ Mounting Plate I/O cables

Warranty
HP standard one-year limited warranty

Country of origin
Taiwan(AC3, ABT); Thailand(AC3, ABT)

What is in the box
HP Poly Studio A2 Table Microphone (Black)
Mounting plate
JST to Phoenix input cable (6 m)
JST to Phoenix daisy-chain output cable (2 m)
JST to JST daisy-chain cable (1.8 m)
Quick start guide
Safety guide
Warranty card

HP Poly Studio A2 Black Table Microphone w/ Mounting Plate I/O cables

Footnotes

Messaging Footnotes

[1] HP Poly Studio A2 Table Microphone support varies by product: Poly Studio G62 supports up to 8; Poly Studio V72/X72 up to 4; Poly Studio V52/X52 up to 4; Poly Studio X32 up to 2; Poly Studio V12 supports 1. Microphone pickup range is up to 14 ft (4.3 m) in radius.
[2] Recycled plastic is expressed as a percentage of the total weight plastic. Post-consumer recycled is based on the definition set in the EPEAT standard for computers, IEEE 1680.1-2018 standard.
[3] Percent of paper-based packaging made from sustainably sourced, certified, and recycled fibers.
[4] HP Poly Studio A2 Table Microphone is compatible with currently available next generation Poly Studio G, V, and X Series products; future compatibility may vary by model.

Technical Specifications Footnotes

[1] Poly Lens Manages the Audio Bridge through the primary Poly video device.
[2] Recycled plastic is expressed as a percentage ofthe total weight plastic. Post-consumerrecycled is based on the definition setin the EPEAT standard for computers, IEEE 1680.1-2018 standard.
[3] Percent of paper-based packaging made from sustainably sourced, certified, and recycled fibers.

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

September 2026
gb-en