LOQ 17IRX10 83JH0000FR

Lenovo

PSREF
Product Specifications Reference

PERFORMANCE

Processor
Intel® Core™ i5-13450HX, 10C (6P + 4E) / 16T, P-core 2.4 / 4.6GHz, E-core 1.8 / 3.4GHz, 20MB

AI PC Category[1]
AI-Powered Gaming PC

Graphics
NVIDIA® GeForce RTX™ 5050 8GB GDDR7, Boost Clock 2662MHz, TGP 115W, 440 AI TOPS

Chipset
Intel® HM770 Chipset

Memory
1x 16GB SO-DIMM DDR5-4800

Memory Slots
Two DDR5 SO-DIMM slots, dual-channel capable

Max Memory[2]
Up to 32GB DDR5-4800 offering

Storage
512GB SSD M.2 2242 PCIe® 4.0x4 NVMe®

Max Storage Support[3]
Up to two drives, 2x M.2 SSD
• M.2 SSD up to 1TB each

Storage Slot
Two M.2 2280 PCIe® 4.0 x4 slots

Card Reader
None

Optical
None

Audio Chip
High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers
Stereo speakers, 2W x2, optimized with Nahimic Audio

Camera
5.0MP with E-shutter

Microphone
2x, Array

Battery
60Wh

Power Adapter
245W Slim Tip (3-pin)

Special Features
AI Chip: LA1

DESIGN

Display[4]
17.3" FHD (1920x1080) IPS 300nits Anti-glare, 100% sRGB, 165Hz, G-SYNC®

Touchscreen
None

Color Calibration
None

Keyboard
White Backlit, French

Touchpad
Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 75 x 120 mm (2.95 x 4.72 inches)

Case Color
Luna Grey

Surface Treatment
Painting

Case Material
PC-ABS (Top), PC-ABS (Bottom)

Pen
Pen Not Supported

Dimensions (WxDxH)[5]
398.4 x 276.2 x 22.95-25.25 mm (15.69 x 10.87 x 0.94-0.99 inches)

Weight[6]
Starting at 2.9 kg (6.39 lbs)

SOFTWARE

Operating System
Windows® 11 Home, French

Bundled Software
Office Trial

CONNECTIVITY

WLAN + Bluetooth®[7]
Wi-Fi® 6, 802.11ax 2x2 + BT5.2

WWAN
Non-WWAN

Ethernet
100/1000M (RJ-45)

Standard Ports
- 4x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with USB PD 65-100W and DisplayPort™ 1.4
- 1x HDMI® 2.1, up to 8K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Ethernet (RJ-45)
- 1x Power connector

Docking
Various docking solutions supported via USB-C®.
For more compatible docking solutions, please visit Docking for LOQ™ 17IRX10

SECURITY & PRIVACY

Security Chip
Firmware TPM 2.0 Enabled

Fingerprint Reader
None

Other Security
E-shutter

SERVICE

Base Warranty
2-year, Courier or Carry-in

Included Upgrade
None

ACCESSORIES

Bundled Accessories
None

CERTIFICATIONS

Green Certifications
- ErP Lot 3
- RoHS compliant

Other Certifications
TÜV Rheinland® Low Blue Light (Software Solution)

MODEL

TopSeller	: No	**Announce Date**	: 2025-06-24
EAN / UPC / JAN	: 198155882548	**End of Support**	: 2031-07-03

Product image is a sample, it may not match the real color of this model
· Lenovo reserves the right to change specifications without notice.
To see more note information, please access the web page.

Premium Care - **Advanced Support from Real People. Real Fast.**

REAL PERSON
Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

REAL FAST
Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

HASSLE FREE
'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

PC HEALTH CHECK
Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - **Protection of your PC from the unexpected.**

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – **Included with the systems you purchase, default 1- or 3-year coverage window.**

Warranty Extensions & Upgrades – **Service and protection that's right for your circumstances.**

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Lenovo **PSREF**
Product Specifications Reference