ThinkStation P2 Tower Gen 2 30JQ0073GE

PSREF
Product Specifications Reference

PERFORMANCE

Processor
Intel® Core™ Ultra 7 265, 20C (8P + 12E) / 20T, Max Turbo up to 5.3GHz, 30MB Intel® Smart Cache

AI PC Category[1]
AI-Ready Workstations

Processor Sockets
1x FCLGA1851

Integrated Graphics
Integrated Intel® Graphics

Discrete Graphics
1x NVIDIA® GeForce RTX™ 5060 8GB

Chipset
Intel® W880 Chipset

Memory
2x 16GB UDIMM DDR5-5600 Non-ECC

Memory Slots
Four DDR5 UDIMM slots, dual-channel capable

Max Memory[2]
Up to 128GB (4x 32GB DDR5 UDIMM)

PCIe® NVMe® Controller
Integrated NVMe® Controller

PCIe® NVMe® Drive
1x 1TB SSD M.2 2280 PCIe® 4.0x4 Performance NVMe® Opal

SATA Controller
Onboard Intel® RSTe SATA RAID

SATA/SAS Drive
None

Optical
None

Audio Chip
High Definition (HD) Audio, Realtek® ALC623-CG codec

Power Supply
500W Platinum Fixed

DESIGN

Keyboard
USB, Calliope, Black, German

Mouse
USB Calliope Mouse, Black

Dimensions (WxDxH)[3]
170 x 315.35 x 376 mm (6.7 x 12.4 x 14.8 inches, with feet)

Weight[4]
9.67 kg (21.32 lbs, maximum configuration)

CONNECTIVITY

Onboard Ethernet
Intel® I219-LM, 1x GbE RJ-45

Optional Ethernet
None

WLAN + Bluetooth®
None

Card Reader
None

Front Ports
- 1x USB-C® (USB 20Gbps / USB 3.2 Gen 2x2), data transfer only
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 1x headphone / microphone combo jack (3.5mm)
- 1x microphone (3.5mm)

Rear Ports
- 2x USB-A (Hi-Speed USB / USB 2.0)
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1), one supports Smart Power On
- 1x HDMI® 2.1 TMDS
- 2x DisplayPort™ 1.4
- 1x Ethernet (GbE RJ-45)
- 1x line-out (3.5mm)

Optional Rear Ports (configured)
None

SECURITY & PRIVACY

Security Chip
Discrete TPM 2.0, TCG certified, FIPS 140-2 certified

Physical Locks
- Kensington® Security Slot™, 3 x 7 mm
- Padlock Loop

Cover Lock
None

Cable Lock
No Cable

Chassis Intrusion Switch
None

MANAGEABILITY

System Management
Intel® vPro® Enterprise with Intel® AMT 16

SERVICE

Base Warranty
3-year, Onsite

Included Upgrade
None

CERTIFICATIONS

ISV Certifications
Please visit ISV certifications for Lenovo® Workstations

SOFTWARE

Operating System
Windows® 11 Pro, German

Bundled Software
Lenovo® AI Now

MODEL

TopSeller	: Yes	**Announce Date**	: 2025-08-13
EAN / UPC / JAN	: 0199272585060	**End of Support**	: 2033-06-15



Product image is a sample, it may not match the real color of this model

Note:
[1] With scalable configurations of higher-performance CPUs and professional NVIDIA RTX GPUs, in addition to advantage of the same modern AI PC technology, AI-Ready workstation power the demanding AI consumption & development workflows.
[2] The max memory is based on the test results with current Lenovo memory offerings.
[3] The system dimensions may vary depending on configurations.
[4] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

· Lenovo reserves the right to change specifications without notice.

To see more note information, please access the web page.

Premier Support - **A direct 24x7x365 line to our most elite technicians.**

- Advanced technical support, 24x7x365, in more than 100 markets
- Technical Account Managers for proactive relationship and escalation management
- Comprehensive hardware & OEM software support
- Priority on service delivery and repair parts
- Single point of contact for simplified end-to-end case management
- Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - **Protection of your PC from the unexpected.**

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - **Included with the systems you purchase, default 1- or 3-year coverage window.**

Warranty Extensions & Upgrades - **Service and protection that's right for your circumstances.**

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo USB-C to Ethernet Adapter

4X90S91831

The Lenovo USB-C to Ethernet Adapter is quick and easy way to connect your USB-C enabled notebook to Ethernet connections. It's ideal for imaging of systems or transferring large files quickly.

Recommended Services

BEST	4Y Premier Support Upgrade from 3Y Onsite (5WS0T36136)
BETTER	3Y Premier Support Upgrade from 3Y Onsite (5WS0U26646)
GOOD	3Y Keep Your Drive Add On (5PS0Q11763)

Please click here to view the full list of accessories.

Lenovo PSREF Product Specifications Reference