Tab K11 Gen 2 ZAFS0024GB

Lenovo

PSREF
Product Specifications Reference

PERFORMANCE

Processor
MediaTek Dimensity 6300 (8C, 2x A76 @2.4 GHz + 6x A55@2.0 GHz)

Graphics
Integrated Arm Mali-G57 MC2 GPU

Chipset
MediaTek SoC Platform

Memory
4GB Soldered LPDDR4x

Storage
128GB UFS 2.2

Card Reader
microSD Card Slot

Max Storage Support
- 128GB UFS 2.2 on systemboard
- microSD card, supports up to 2TB (exFAT)

Speakers
4 speakers, optimized with Dolby Atmos®

Microphone
Mono

Camera
Front 8.0MP / Rear 13.0MP with Flashlight

VoiceCall
No

Sensors
- Accelerometer sensor
- Ambient light sensor (ALS)
- Hall sensor

Vibration Motor
No support

Battery
7040mAh (Typical)

Power Adapter
10V / 2A

DESIGN

Display[1]
11″ 2.5K (2560x1600) IPS 500nits Anti-fingerprint, 72% NTSC, 90Hz, Touch

Touchscreen
In-cell, 10-point Multi-touch

Case Material
Metal

Keyboard
None

Pen
Pen Upgradable (Purchase Separately)

Dimensions (WxDxH)[2][3]
254.59 x 166.15 x 6.99 mm (10.02 x 6.54 x 0.28 inches)

Weight[4]
480 g ± 10 g (1.06 lbs ± 0.02 lbs)

Case Color
Luna Grey

SOFTWARE

Operating System[5]
Android™ 15 or Later

CONNECTIVITY

WLAN + Bluetooth®
Wi-Fi® 5, 802.11ac 1x1 + BT5.2

WWAN
Non-WWAN

SIM Card
No Support

Location Services
GPS + GLONASS + Galileo

Standard Ports
- 1x USB-C® (Hi-Speed USB / USB 2.0), with charging
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Card slot

SERVICE

Base Warranty[6]
1-year, Courier

ACCESSORIES

Bundled Accessories
None

CERTIFICATIONS

Green Certifications
- Energy rating E (TB336FU). View details by EPREL registration number 2303451.
- ENERGY STAR® 9.0 (only available for TB336FU)
- ErP Lot 6/26
- RoHS compliant

Dust and Water Resistant
IP52

Other Certifications
- TÜV Rheinland® Flicker Free
- TÜV Rheinland® Low Blue Light (Hardware Solution)

MODEL

Product	: TB336FU		
TopSeller	: Yes	**Announce Date**	: 2025-04-23
EAN / UPC / JAN	: 198157012691		

Product image is a sample, it may not match the real color of this model

Note:
[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.
[2] The system dimensions may vary depending on configurations.
[3] The height is 8.29 mm (0.33 inches) with the camera bump.
[4] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.
[5] For latest operating system and security patches deliver plan, please visit https://support.lenovo.com/solutions/ht501098.
[6] For warranty upgrade service, please go to https://smartfind.lenovo.com/services. To learn more details of warranty policy, please access https://support.lenovo.com/warrantylookup/warrantypolicy.

· Lenovo reserves the right to change specifications without notice.

To see more note information, please access the web page.

Premium Care - **Advanced Support from Real People. Real Fast.**

REAL PERSON
Choose how you want to reach us – through phone, chat, or email – our expert technicians will take care of your device issues.

REAL FAST
Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If the issue can't be solved remotely, our team will schedule a repair via depot / carry-in support to resolve your issue.

HASSLE FREE
'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach – that's how Premium Care delivers you the ideal support experience.

Accidental Damage Protection One - **Protection for your Tablet from the unexpected.**

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your Tablets, permitting a single repair during the coverage period.

Base Warranty - **Included with the system you purchase with default 1-year coverage window.**

Lenovo Warranty Extensions & Upgrades (up to 3 years duration)
- Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

- Pick up & return courier / Depot support
- Replaceable unit service*

*Applicable in some regions only. Please check with your local services team for more details.

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.