Datasheet

HP OfficeJet Pro 9135 All-in-One Printer

Print like you mean business

HP's fastest inkjet printers help your small business do more. Enjoy professional-quality prints and advanced features that keep work moving smoothly, while keeping your data protected with HP Wolf Security.[2]

This printer is intended to work only with cartridges that have a new or reused HP chip, and it uses dynamic security measures to block cartridges using a non-HP chip. Periodic firmware updates will maintain the effectiveness of these measures and block cartridges that previously worked. A reused HP chip enables the use of reused, remanufactured, and refilled cartridges. More at: http://www.hp.com/learn/ds

ISO Speed: Black: Up to 25 ppm; Color: Up to 20 color ppm
Print Resolution: Black (best): Up to 1200 x 1200 rendered dpi; Color (best): Up to 4800 by 1200 optimized dpi on HP Advance Photo Paper 1200 by 1200 dpi input
Scan Resolution: Hardware: Up to 1200 x 1200 dpi; Optical: Up to 1200 dpi
Copy Resolution: Black (text and graphics): Up to 600 dpi; Color (text and graphics): Up to 600 dpi
Standard Connectivity: 1 Ethernet; 1 Hi-Speed USB 2.0 (device); 1 Hi-Speed USB 2.0 (host); 1 Wi-Fi 802.11 a/b/g/n/ac (dual band); 2 RJ-11 Fax/Modem port/phone line
Mobile Printing Capability: Chrome OS; HP app; Apple AirPrint™; Wi-Fi® Direct Printing; Mopria™ certified
Duty cycle: Monthly, letter: Up to 30,000 pages; Monthly, A4: Up to 30,000 pages
Display: 4.3" intuitive touchscreen Color Graphic Display (CGD)
Paper Handling: Input Capacities: Up to 500 sheets Standard; Output Capacities: Up to 100 sheets Standard

Keep busy teams productive

- Boost productivity with print speeds up to 25 pages per minute (PPM).[1]
- Save time with single-pass, double-sided scanning using the automatic document feeder.
- HP AI helps you simplify tasks, personalize experiences, and enhance productivity.[4]

Business-ready color for all your print needs

- From flyers to presentations, your printer is ready for whatever the job demands.
- Produce water-resistant, smear-resistant, and fade-resistant prints.[6]

Save money, save time with Instant Ink[7]

- Never worry about running out of ink! With Instant Ink, you get ink delivered right to your door.[7]
- Enjoy the freeedom to choose a plan that fits your needs—with the flexibility to change, pause, or cancel anytime.[8]
- Whether you print in full color or black & white—every page costs the same with Instant Ink.

The most reliable printers[5]

- Achieved zero jams, misfeeds, device errors, and machine malfunctions across thousands of test pages.[5]
- Unlike competitors, optimized for recycled paper to boost device reliability.[5]

[1] Excludes first set of ISO test pages. For details, see: www.hp.com/go/printerclaims . [2] OfficeJet Pro 8100, 9100, 9730 print speeds compared to other HP inkjet printers. [3] HP Smart and myHP are now the HP app, available for download on Windows 10 or 11 PCs; macOS computers; and for Apple and Android mobile phones and tablets. Windows PCs do not support print features at launch. Android not supported in China at launch. The HP app requires download available at www.hp.com/hp-app. Not all HP devices, services, apps are available in the HP app. Certain features are available in English language only, and may vary by printer and PC model/country, and between desktop/mobile applications. HP reserves the right to introduce charges for use of select HP app functionality. Internet access required. HP account required for full functionality. Fax sending capability only. Live chat and phone support are available during business hours and varies by country. Chat service is localized in supported regions, and where not supported, will default to English. Supported conferencing features vary by device and device configuration. For complete Terms of Service see: www.hp.com/hp-app-terms-of-use . [4] Requires optional HP AI software to use artificial intelligence (AI). Certain HP AI features are available in English only, and may vary by printer model/country, and between desktop/mobile applications. Requires HP app or HP Easy Start and being signed into your HP account or Smart Admin account. Internet access is required. Some features may be beta apps. HP reserves the right to charge for these and additional services in the future in accordance with the HP AI Terms of Service. To learn more, visit hp.com/HP_AI . [5] Compared to the top-shipping wireless A4 color MFP ink tank printers for Epson, Canon, and Brother under $450 USD in Developed Markets (USA, Canada, W.Europe). Printers selected by market share as reported by IDC Quarterly Hardcopy Peripherals Tracker – Final Historical CYQ2 2025. Testing was conducted in distinct groups. Claim based on Keypoint Intelligence hands-on testing and study commissioned by HP in September 2025. For details, please see: keypointintelligence.com/hpmostreliableprinters. [6] When used with Original HP inks. Based on internal testing, ISO 11798 certification, and Wilhelm Imaging Dark Storage statement. Performance may vary depending on media and ink selection. See hp.com/go/printpermanence for details. [7] Savings Claim: Based on monthly subscription cost of HP Instant Ink 700-page plan without purchase of additional sets of pages compared to cost per page (CPP) to print ISO/IEC 24711 pages on most HP, A4 color inkjet cartridge printers and MFPs. Comparative printers are priced at or below the most expensive HP Instant-Ink eligible printer in each country using local currency, annually. Sale prices not considered for this study. Average CPP per country used to determine percent savings versus CPP for HP Instant Ink. HP Ink Advantage printers, printers sold through contract, and other printers which only use XL cartridges excluded due to non-standard hardware & supplies model. Keypoint Intelligence annual study commissioned by HP. Printers selected by market share in IDC Quarterly Hardcopy Peripherals. www.keypointintelligence.com/HPInstantInk . Automatic Delivery: Based on plan usage, Internet connection to eligible HP printer, valid payment method, email address, and delivery service in your geographic area. Never Run Out: Printers require direct connection to the Internet for program participation. Internet access sold separately. [8] Change or cancel your plan at any time online. If you decide to cancel your HP Instant Ink plan you can use HP original Standard or XL cartridges and, for non-HP+ printers, you can use HP original Standard or XL cartridges or 3rd party cartridges that are compatible with your HP printer. Plan upgrades are effective immediately and the charges will be applied retrospectively or in the next billing cycle, depending on user choice. Plan downgrades and cancellations are effective after the last day of the current billing period. For full details go to hpinstantink.com/terms . [9] Select "Plain Paper, Light/Recycled" as the paper type in your printer settings for optimal results. [10] Internet access required and must be purchased separately. Wireless operations are compatible with 2.4 GHz and 5.0 GHz operations only. Learn more at www.hp.com/go/mobileprinting .

HP OfficeJet Pro 9135 All-in-One Printer Technical specifications

Functions	Print, copy, scan, fax
Multitasking supported	Yes
Print speed[5]	**Letter:** Up to 25 ppm; **Black (ISO):** Up to 25 ppm; **Color (ISO):** Up to 20 ppm; **First page out black:** As fasts as 10 sec; **First Page Out Color:** As fasts as 11 sec; **Black (draft):** Up to 39 ppm; **Color (draft):** Up to 39 ppm; **Print speed Black Duplex:** Up to 15 ipm; **Print speed Color Duplex:** Up to 13 ipm
Print resolution	**Black (best):** 1200 x 1200 rendered dpi; **Color (best):** Up to 4800 x 1200 optimized dpi on HP Advance Photo Paper 1200 x 1200 dpi input
Print technology	HP Thermal Inkjet
Print resolution technologies	HP Thermal Inkjet
Print cartridges number	4 (1 each black, cyan, magenta, yellow)
Borderless printing	Yes, on photo paper only, up to 8.5 x 11 in (US letter), 210 x 297 mm (A4)
Standard print languages	HP PCL3 GUI
Printer smart software features	Orientation: Portrait/Landscape; Print on Both Sides: None/Flip on Long Edge/Flip on Short Edge; Page Order: Front to Back/Back to Front; Pages per Sheet: 1, 2, 4, 6, 9, 16; Quality Settings: Draft/Normal/Best; Printing Shortcuts; Print in Grayscale: Off/High Quality Grayscale/Black Ink Only; Pages per Sheet Layout: Right then Down/Down then Right/Left then Down/Down then Left; Print in Max DPI: No/Yes; HP Real Life Technologies: Off/On; Booklet: None/Booklet-Left Binding/Booklet-Right Binding; Pages to Print: Print All Pages/Print Odd Pages Only/Print Even Pages Only; Borderless Printing: Off/On; Page Borders: Off/On
Scan type / Scan technology	Easy slide-off glass, single-pass 2-sided ADF / Contact Image Sensor (CIS)
Scan resolution	**Hardware:** Up to 1200 x 1200 dpi; **Optical:** Up to 1200 dpi
Scan file format	JPG, BMP, TIFF, PDF, RTF, TXT, PNG
Scan input modes	Front-panel scan, copy, HP Software, EWS, Mobile apps
Scan size maximum	**ADF** 8.5 x 14 in ; 215.9 x 355.6 mm ; **Flatbed** 8.5 x 11.7 in ; 215.9 x 297 mm
Scan speed	Up to 18 ipm (200 ppi, b&w); Up to 18 ipm (200 ppi, color)
Scanner advanced features	Smart Tasks shortcuts: 1-click customizable scan to cloud destinations, email, and print; Smart Tasks destinations: Dropbox, Google Drive, OneDrive, email recipients
Bit depth / Grayscale levels	24-bit/ 256
Digital sending standard features	Scan-to E-mail; Scan to network folder; Scan to SharePoint; Scan to thumb drive
Copy speed	**Black (ISO):** Up to 23 cpm; **Color (ISO):** Up to 15 cpm; **Black (draft):** Up to 33 cpm; **Color (draft):** Up to 22 cpm
Copy resolution	**Black (text and graphics):** Up to 600 dpi; Up to 600 dpi; **Color (text and graphics):** Up to 600 dpi
Maximum number of copies	Up to 99 copies
Copier settings	Number of Copies; Two-Sided; Lighter/Darker; HP Copy Fix; ID Copy; Resize; Quality; Paper Size; Paper Type; Collate; Margin Shift; Crop; Copy Preview; Tray Select; Enhancements
Copier resize	25 to 400%
Fax resolution	**Black (best):** 300 x 300 dpi; **Color (best):** 200 x 200 dpi; **Black (standard):** 200 x 100 dpi; **Color (standard):** 200 x 200 dpi
Fax speed	4 sec per page
Fax Features	**Fax memory Letter:**Up to 100 pages; **Fax memory A4:**Up to 100 pages; **Auto fax reduction supported:** Yes; **Auto-redialing:** Yes; **Fax delayed sending:** Yes; **Distinctive ring detection supported:** Yes; **Fax forwarding supported:** Yes (black only); **Fax phone TAM interface supported:** No; **Fax polling supported:** No; **Fax telephone mode supported:** No; **Junk barrier supported:** Yes; **Maximum speed dialing numbers:** Not Supported; **PC interface supported:** Yes, HP Software support provided; **Remote retrieval capability supported:** No; **Telephone handset supported:** No
Standard connectivity	1 Ethernet; 1 Hi-Speed USB 2.0 (device); 1 Hi-Speed USB 2.0 (host); 1 Wi-Fi 802.11 a/b/g/n/ac (dual band); 2 RJ-11 Fax/Modem port/phone line
Network capabilities	Yes, via built-in Ethernet; Wireless 802.11a/b/g/n/ac
Wireless capability	Yes, with built-in dual-band Wi-Fi 802.11 a/b/g/n/ac and a self-heal solution
Mobile printing capability[4]	Chrome OS; HP app; Apple AirPrint™; Wi-Fi® Direct Printing; Mopria™ certified
MemoryNone	**Standard:** 512 MB; **Maximum:** 512 MB
Processor speed	1.2 GHz/**Hard disk:** No Hard Disk
Duty cycle[7]	**Monthly, letter:** Up to 30,000 pages; **Monthly, A4:** Up to 30,000 pages
Recommended monthly page volume	Up to 2000
Media types supported	Tray 1: Plain Paper, HP Photo Papers, HP Matte Brochure or Professional Paper, HP Matte Presentation Paper, HP Glossy Brochure or Professional Paper, Other Photo Inkjet Papers, Other Matte Inkjet Papers, Other Glossy Inkjet Papers, Thick Plain Paper, Light/Recycled Plain Paper, HP Tri-fold Brochure Paper, Glossy. Tray 2: Plain Paper.
Media weight supported	16 to 28 lb (plain paper); 60 to 75 lb (photo); 20 to 24 lb (envelope); 90 to 110 lb (card)
Media sizes supported	Tray 1:Letter, Legal, Government Legal; Executive; Statement; 3 x 5 in; 4 x 6 in; 5 x 7 in; 13 x 18 cm; 8 x 10 in; 10 x 15 cm; L; Photo 2L; Envelope(#10, Monarch, 5.5 bar); Card (3 x 5 in, 4 x 6 in, 5 x 8 in) Tray 2:Letter; Legal.
Media Sizes Custom	Tray 1: 3 x 5 to 8.5 x 14; 5 x 8.3 to 8.5 x 14 in. Tray 2: N/A
Paper handling	**Input Capacities:** Up to 500 sheets (Tray 1: up to 250 sheets, Tray 2: up to 250 sheets) Standard; Up to 30 envelopes; Up to 50 cards; Up to 50 sheets Labels; Up to 250 sheets Legal **Auto Document Feeder:** Standard, 35 sheets **Output Capacities:** Up to 100 sheets Standard; Up to 10 envelopes; Up to 30 cards; Up to 30 sheets Labels; Up to 100 sheets Legal **Duplex Options:** Automatic **Envelope feeder:** No **Standard paper trays:** 2
What's in the box	**C2WM0A** HP OfficeJet 9135 All-in-One Printer; HP 936 Setup Black Ink Cartridge (~800 pages); HP 936 Setup Cyan Ink Cartridge (~420 pages); HP 936 Setup Magenta Ink Cartridge (~420 pages); HP 936 Setup Yellow Ink Cartridge (~420 pages); Regulatory Flyer; Ink Caution Flyer; Power Cord; Setup Poster; Reference Guide [For more information about fill and yield, see http://www.hp.com/go/learnaboutsupplies]
Page yield (set-up/inbox cartridges)	~800 pages black, ~420 pages cyan, magenta, yellow composite
Replacement cartridges	HP 936 Black Original Ink Cartridge (~1,250 pages) 4S6V2LN, HP 936 Cyan Original Ink Cartridge (~800 pages) 4S6U9LN; HP 936 Magenta Original Ink Cartridge (~800 pages) 4S6V0LN; HP 936 Yellow Original Ink Cartridge (~800 pages) 4S6V1LN. HP EvoMore planned to be available April 2024: HP 936e EvoMore Black Original Ink Cartridge (~2,500 pages) 4S6V6LN; HP 936e EvoMore Cyan Original Ink Cartridge (~1,650 pages) 4S6V3LN; HP 936e EvoMore Magenta Original Ink Cartridge (~1,650 pages) 4S6V4LN; HP 936e EvoMore Yellow Original Ink Cartridge (~1,650 pages) 4S6V5LN. Actual yield varies considerably based on content of printed pages and other factors. For details, see https://www.hp.com/go/learnaboutsupplies .
Product dimensions	**W x d x h:** 17.20 x 15.60 x 12.53 in (Minimum Storage Mode) /437 x 396.3 x 318.3 mm (Minimum Storage Mode) ; **Maximum:** 17.20 x 21.54 x 12.53 in (Output Tray Extend) /437 x 547 x 318.3 mm (Output Tray Extend)
Product weight[2]	~ 26.10 lb
Warranty features	One-Year limited hardware warranty. For more info please visit us at http://support.hp.com .[8]
Energy efficiency compliance	IT ECO Declaration; EPEAT® registered
Energy star certified	Yes
Sustainable impact specifications	Recyclable through HP Planet Partners
Control panel	4.3" (10.92 cm) touchscreen control panel with CGD (color graphic display)
Display description	4.3" intuitive touchscreen Color Graphic Display (CGD)
Software included	HP Printer Software
Web solutions	Wolf Pro Security, Scan to Email, HP app
Compatible operating systems	Windows 11; Windows 10; Windows Server; macOS 11 Big Sur; macOS 12 Monterey; macOS 13 Ventura; macOS 14 Sonoma; Linux; Chrome OS
Compatible network operating systems	Windows 11; Windows 10; Windows Server; macOS 11 Big Sur; macOS 12 Monterey; macOS 13 Ventura; macOS 14 Sonoma; Linux; Chrome OS
Minimum system requirements	**PC:** Windows 10, 11: 32-bit or 64-bit, 2 GB HD, Internet Required, Internet Explorer or Edge; **Mac:** Apple macOS v11 Big Sur, macOS v12 Monterey, macOS v13 Ventura, 2 GB HD, Internet required
Power[3]	**Power supply type:** Internal (Built-in) Universal Power Supply; **Power requirements:** Input voltage: 100 to 240 VAC (+/- 10%), 50/60 Hz; **Power consumption:** 5.58 watts (ready), 1.22 watts (sleep), 0.14 watts (manual-Off)
Acoustics	**Acoustic power emissions:** 7.0 B(A) (printing at 21ppm); **Acoustic pressure emissions:** 61 dB(A) (printing at 21ppm)
Operating environment	**Operating temperature range:** 41 to 104°F; **Recommended operating temperature:** 59 to 90°F; **Storage temperature range:** -40 to 140°F; **Operating humidity range:** 20 to 80% RH; **Recommended humidity operating range:** 25 to 75% RH
HP Service and Support options	UQ211E - HP 2y NBD Advance Exchange OJ H SVC; UQ212E -
Country of origin	Thailand(B1H)

Learn more at
hp.com

[1] Dimensions vary as per configuration [2] Weight varies as per configuration [3] Power requirements are based on the country/region where the printer is sold. Do not convert operating voltages. This will damage the printer and void the product warranty. [4] Wireless performance is dependent upon physical environment and distance from the access point. Wireless operations are compatible with 2.4 GHz routers only; excludes wireless direct. Wireless direct may require driver or apps be installed and connected on wireless-enabled mobile device or PC. Wireless functionality may vary by computer and mobile operating systems, see hpconnected.com. HP ePrint requires: account registration, HP ePrint-enabled printer, Internet connection, and a wireless-enabled mobile device or Internet-connected computer with email capability. Separately purchased data plans or usage fees may apply. Print times and connection speeds may vary. AirPrint supports OS X® Lion, OS X® Mountain Lion and the following devices running iOS 4.2 or later: iPad®, iPhone® (3GS or later), iPod touch® (3rd generation or later) and requires the printer be connected to the same network as your OS X or iOS device. AirPrint, the AirPrint Logo, iPad, iPhone, and iPod touch are trademarks of Apple® Inc. Windows is a trademark of the Microsoft group of companies. BlackBerry® names and logos are the property of Research In Motion Limited. Android is a trademark of Google Inc. [5] Speed specifications have been updated to reflect current industry testing methods. 6] Either after first page or after first set of ISO test pages. For details see http://www.hp.com/go/printerclaims [7] HP recommends that the number of printed pages per month be within the stated range for optimum device performance, based on factors including supplies replacement [8] For full terms and conditions visit: www.hp.com/go/orderdocuments . Warranty and support options vary by product, country, and local legal requirements.