MPN: MO-UACC-OM-SFP28-SR

SFP28 25 Gbps, MMF, 100m, LC duplex, DOM support, Compatible with UACC-OM-SFP28-SR

Micro-Optics products provide seamless connectivity for all your current and future network hardware needs.

- **100% Ubiquiti Compatible**

Specifications

Features	**Brand compatibility**	Ubiquiti Networks
	Certification	MSA
	Compatible products	Ubiquiti UACC-OM-SFP28-SR
	Easy to install	Yes
	Form factor	SFP28
	Hot-Plug support	Yes
	Hot-swap	Yes
	Plug and Play	Yes
	RoHS compliance	Yes
Legal Information	**Country of Origin**	Japan
	EU ECCN Code	N/A
	Tariff No.	8517790000
	UNSPSC Code	43201553
	US ECCN Code	5A992
Operational conditions	**Operating temperature (T-T)**	-45 - 75 °C
	Storage relative humidity (H-H)	10 - 85 %
	Storage temperature (T-T)	-40 - 85 °C
Package dimensions	**Depth (package,cm)**	10 cm
	Gross Weight (Package, kg)	0.15 kg
	Height (package,cm)	3 cm
	Width (package,cm)	6 cm
Packaging data	**Number of products included**	1 pc(s)
Performance	**Digital Diagnostics Monitoring (DDM)**	Yes

Performance	**Duplex system**	Full
	Ethernet interface type	25 Gigabit Ethernet
	Fiber ethernet cabling technology	25GBASE-SR
	Fiber optic connector	LC
	Fiber ports quantity	1
	Interface type	SFP28
	Maximum data transfer rate	25000 Mbit/s
	Maximum transfer distance	100 m
	Multi-mode fiber (MMF) supported	Yes
	SFP transceiver type	Fiber optic
	Single-mode fiber (SMF) supported	No
	Wavelength	850 nm
Product dimensions	**Net Weight (Product, kg)**	0.1 kg
	Product Depth	4.5 cm
	Product Height	1.1 cm
	Product Width	1.4 cm
Vendor information	**Brand Name**	Lanview
	Warranty	5 Year(s)

Other products in this series

Maximum transfer distance	Cisco	D-Link	Dell	Extreme Networks
2				
3	MO-SFP-25G-AOC3M-GREY			
5	MO-SFP-H25GB-CU5M			
10	MO-SFP-25G-AOC10M		MO-CBL-25GSFP28-AOC-10M	
100	MO-SFP-25G-SR-S	MO-DEM-S2801SR	MO-407-BBXU	MO-7G17A03537
300				
400			MO-DELL-SFP28-25G-ESR	
3000				
10000	MO-SFP-10/25G-LR-S		MO-D-SFP28-25GLR-31	MO-10504

Maximum transfer distance	Finisar	Fortinet	Generic	HP
2				
3				
5				
10				MO-Q9S69A
100			MO-G-SFP-25G-SR	MO-845398-B21
300				MO-JL485A
400				
3000				
10000	MO-FTLF1436P3BCL	MO-FG-TRAN-SFP28-LR	MO-G-SFP-25G-LR	MC-EC-SFP28-25G-LR

Maximum transfer distance	Huawei	Intel	Juniper	Lenovo
2				
3				
5				
10				
100	MO-02311KNR	MO-E25GSFP28SR	MO-JNP-SFP-25G-SR	

Maximum transfer distance	Huawei	Intel	Juniper	Lenovo
300				
400				
3000	MO-02313JFQ			
10000		MO-E25GSFP28LRX		MO-LP32-LW-OPT

Maximum transfer distance	Mellanox	NetApp	NETGEAR	Nvidia
2		MO-X66240A-2		
3		MO-X66240A-3		
5				
10				
100	MO-MMA2P00-AS-SP		MO-NET-25GBASE-SR	
300				
400				
3000				
10000			MO-NET-25GBASE-LR-S	MO-MMA2L20-AR

Maximum transfer distance	Palo Alto Networks	QLogic	Ruckus Wireless	Ubiquiti Networks
2				
3				
5				
10				
100	MO-PAN-SFP28-25GBASE-SR	MO-SFP32-SR-SP-C	MO-RUC-E25G-SFP28-SR	MO-UACC-OM-SFP28-SR
300				
400				
3000				
10000			MO-RUC-E25G-SFP28-LR	MO-UACC-OM-SFP28-LR

Other images