MPN: 0070-10403-A4

Cygnus 16 channel 4 Bay Hybrid NVR - Supports AHD, TVI, CVI, CVBS, IP video inputs - NDAA



Supports AHD, TVI, CVI, CVBS, IP video inputs
- Max 24-ch IP camera inputs , each channel up to 5MP
- Up to 4K-N/5MP resolution for recording
- Support HDMI and VGA output
- Smart search and playback
- Support multiple languages
- Easy to use same Interface of GUI/WEB

Analog Video Input 16-ch BNC
AHD Input 8MP, 5MP, 4MP, 3MP, 1080P, 720P, D1
TVI Input 8MP, 5MP, 4MP, 3MP, 1080P, 720P, D1
CVI Input 8MP, 5MP, 4MP, 3MP, 1080P, 720P, D1
CVBS Input PAL/NTSC
IP Video Input 16+8ch, each channel up to 5MP
Audio In/Out 6/1
Two-way Talk N/A
HDMI Output 3840×2160, 1920×1080, 1280×1024, 1024×768
VGA Output 1920×1080, 1280×1024, 1024×768
CVBS Output Support
Synchronous Playback 16/9/4/1

Specifications

Battery	**Battery Weight (g)**	3 g
	Lithium Weight (g)	0.064 g
Features	**NDAA Compliance**	Yes
Legal Information	**ADR Information**	UN3091 - Lithium METAL (inside equiment)
	Country of Origin	Taiwan
	Tariff No.	8521900000
Package dimensions	**Gross Weight (Package, kg)**	3 kg
Performance	**Video input channels**	24 channels
Ports & interfaces	**BNC video input**	Yes
	BNC video output	Yes
	Ethernet LAN (RJ-45) ports	2
	Ethernet LAN data rates	10/100/1000 Base-T/TX Mbit/s
	HDMI ports quantity	1
Power	**AC input voltage**	230 V
Product dimensions	**Net Weight (Product, kg)**	1.8 kg
Storage	**Number of HDDs supported**	4
Vendor information	**Brand Name**	Ernitec

Vendor information	**Warranty**	5 Year(s)