

Solar Charger 100W Lightweight

Item no.:

421-45

EAN: 5705730421457
















Sandberg Solar Charger 100W Lightweight is a high-performance solar charger for users who need serious power when away from electrical outlets. The foldable design combines high output with portability, making the panel suitable for outdoor, camping and off-grid use. The monocrystalline PERC solar cells deliver up to 100W, allowing you to charge laptops, power stations, powerbanks and other demanding devices directly from the solar panel via USB-C, USB-A or DC output. The high efficiency ensures stable power delivery under varying conditions. Built with durable ETFE lamination and a robust construction, Sandberg Solar Charger 100W Lightweight is the ideal choice when you need maximum flexibility and high output from solar energy.

More information:
www.sandberg.world

Product Sheet 421-45 en - v2.17

Sandberg Solar Charger 100W Lightweight

Specifications

Solar panel: 100W (Monocrystalline PERC)
IP67 water-, dust- and shockproof
ETFE lamination. Folding 4 pcs. panels
Efficiency: ?157W/sqm
Output ports:
1 x USB-A (QC 3.0): 5V/3.4A, 9V/2.5A, 12V/2A (24W max)
1 x USB-C PD: 5V/3A, 9V/3A, 12V/3A, 15V/3A, 20V/3.25A (65W max)
DC 5521
DC cable 3 meters: 22V / 4.54A (100W max)
Size folded: 442 x 396 x 40 mm
Size open: 442 x 1437 x 22 mm
Weight: 2.9 kg

Press quotes

Packaging info

1 Sandberg Solar Charger 100W Lightweight
4 Snap hooks
1 Quick guide

Quick guide: https://sandberg.world/mt/manual/421-45

Dimensions

	Product	Package
Height (cm)	44.20	41.70
Width (cm)	39.60	45.70
Depth (cm)	4.00	6.70
Weight (g)	2,900.00	3,200.00

Product:
www.sandberg.world/product/solar-charger-100w-lightweight

Dealer: