Eco-conscious 27" IPS monitor with ergonomic stand for modern workplaces

The ProLite XB2793HSU is perfect if you need a compact, high-performance monitor that fits seamlessly into a multi-screen workspace. The four-side ultra-slim bezel design gives you a clean, modern desk setup and uninterrupted viewing across displays.

You'll enjoy sharp detail, vivid colours and wide viewing angles with the IPS panel, while the 120Hz refresh rate keeps everything smooth and responsive. Flicker-free technology and a blue light reducer support your eye comfort during long hours of use.

The fully adjustable ergonomic stand helps you stay comfortable and focused, with 15cm height adjustment plus tilt, swivel and pivot functions, so you can easily set the screen to match your posture.

Built-in speakers, a two-port USB hub, HDMI and DisplayPort inputs, and a headphone socket keep your workspace simple and connected. With EPEAT registration, TCO10 compliance and an Energy Label C rating, it's a smart, sustainable choice that works as hard as you do.

Multi-screen setup for a panoramic workspace

Connect multiple ultra-slim bezel monitors to create a panoramic workspace, keep your apps in view, streamline multitasking, and boost productivity.

Versatile connectivity for all your devices

Connect multiple devices and accessories in one simple step with HDMI, DisplayPort and the USB hub, streamlining your workspace for maximum efficiency and ensuring a tidy, uninterrupted workflow.

Built-in audio without extra clutter

Enjoy clear, pleasant sound for calls, videos, and music while keeping your desk free of extra speakers, thanks to the integrated audio.

Adjustable stand for optimal comfort

Find your perfect screen position easily and maintain a healthy, comfortable posture all day long.

Thanks to its fully adjustable stand, you can effortlessly adapt the monitor to your needs. Raise or lower the height, swivel left or right, or tilt the screen to reduce glare and find the optimal viewing angle. Whether you're working, designing, or attending long video calls, this flexibility helps reduce neck and back strain, improving both comfort and productivity throughout your day.

SPECIFICATION

01 CHARAKTERISTIKA OBRAZU

Design	4-side slim bezel
Úhlopříčka monitoru	27", 68.6cm
Panel	IPS Panel Technology LED s matnou povrchovou úpravou
Nativní rozlišení	1920 x 1080 @120Hz (2.1 megapixel Full HD)
Formát obrazu	16:9
Jas	350 cd/m²
Kontrast	1500:1
Pokročilý kontrast	80M:1
Čas rekace (MPRT)	1ms
Úhel sledování	horizontální/vertikální: 178°/178°, na parvo/na lefo: 89°/89°, nahoru/dolů: 89°/89°
Barevná podpora	16.7mln (sRGB: 96%; NTSC: 72%)
Horizontalfrequenz	30 - 140kHz
Arbeitsfläche H x B	597.9 x 336.3mm
Velikost bodů	0.311mm
Barva	matná, černá

02 ROZHRANÍ / KONEKTORY / OVLÁDÁNÍ

Vstupní porty	HDMI x1 (v.1.4) DisplayPort x1 (v.1.2)
USB HUB	x2 (v. 2.0 (DC5V, 500mA))
HDCP	ano
Konektor pro sluchátka	ano

03 VLASTNOSTI

Redukce modrého světla	ano
Flicker Free LED	ano
Adaptive Sync support	HDMI/DP 1920x1080 @120Hz
Extra	i-Style colour
Jazyky OSD	EN, DE, FR, ES, IT, RU, JP, CZ, NL, PL, UA
Kontrolní tlačítka	Joystick: Centre: Power/Menu, Up/Signal Select, Down, Left/Submenu, Right/Volume
Nastavitelné parametry	picture adjust (brightness, contrast, ECO, ACR, OD, motion blur reduction, Adaptive Sync), colour settings (i-Style colour, blue light reducer, RGB range, colour temperature, user preset), OSD (OSD H. position, OSD V. position, OSD rotate, OSD time, OSD background, DDC/CI control, display information), language, extra1 (sharpness, video mode adjust, opening logo, power LED), extra 2 (shortcut key, FW version), input select, audio settings (volume, mute audio), reset (reset all)
Reproduktory	2 x 2W
Výhoda	Kensington-lock™ připraven, DDC/CI, DDC2B, Mac OSX

04 MECHANICKÉ ČÁSTI

Úpravy polohy	výška, swivel, náklon, Pivot (rotace na obě strany)
Výškově nastavitelné	150mm
Otočný (Pivot)	90°
Úhel otočení	360°; 180° na lefo; 180° na parvo
Úhel náklonu	23° nahoru; 5° dolů
VESA	100 x 100mm
Systém správy kabelů	ano

05 ZAHRNUTÉ PŘÍSLUŠENSTVÍ

Kabely	napájecí (1.8m), USB (1.5m), HDMI (1.5m)
Ostatní	uživatelský manuál, instrukce bezpečnosti

06 POWER-MANAGEMENT

Napájecí zdroj:	interní
Napájení	AC 100 - 249V, 50/60Hz
Odběr energie	14W default , 0.5W odpočinek, 0.3W vypnutý
Odběr energie:	0.5W odpočinek

07 UDRŽITELNOST

Předpisy	TCO Certified, CE, TÜV-GS, EAC, VCCI-B, PSE, RoHS support, ErP, WEEE, REACH, UKCA
Energetická třída (Regulation (EU) 2017/1369)	C
EPEAT Silver	*registration varies by country, go to www.epeat.net for details

08 ROZMĚRY / HMOTNOST

Rozměry výrobku Š x V x D	611.5 x 404 (547.5) x 224.5mm
Rozměry balení Š x V x D	691 x 442 x 142mm
Váha (bez balení)	6.0kg
Váha (s balením)	7.8kg
EAN code	4948570126705

GALERIE

iiyama
ProLite
XB2793HSU
27"
68.6cm
IPS
1920x1080
SLIM BEZEL
15cm
C
A
G
epeat
SILVER
TCO

iiyama
ProLite
XB2793HSU
27"
60.5cm
IPS
1920x1080
SLIM BEZEL
15cm

iiyama
ProLite
XB2793HSU
27"
68.6cm
IPS
1920x1080
SLIM BEZEL
15cm
epeat
SILVER
TCO

iiyama
ProLite
XB2793HSU
27"
68.6cm
IPS
1920x1080
SLIM BEZEL
15cm

iiyama
ProLite
XB2793HSU
27"
68.6cm
IPS
1920x1080
SLIM BEZEL
15cm



Všechny ochranné známky jsou registrovány a chráněny. Vyhrazené právo na změny. Veškeré ploché panely LCD splňují normu ISO-9241-307:2008 v oblasti počtu vadných pixelů. **© IIYAMA CORPORATION. ALL RIGHTS RESERVED**