ThinkVision T24-40 Monitor 64A4MAR2U1

Lenovo

The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- 23.8-inch IPS display
- 99% sRGB and 99% BT.709 color gamut and 48-120Hz variable refresh rate
- USB Hub - Downstream 3 x USB-A 3.2 Gen1, 1x USB-C®® 3.2 Gen 1 (PD 15W data only); Upstream 1 x USB-B 3.2 Gen 1
- TÜV Rheinland®® 5-star Eye Comfort Certification and EyeSafe Certification 2.0
- Ergonomic stand with LTPS (lift, tilt, pivot, and swivel functions)
- Case color - Eclipse Black
- 3-year limited warranty

Premium Care - Advanced Support from Real People. Real Fast.

REAL PERSON
Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

REAL FAST
Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

HASSLE FREE
'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

PC HEALTH CHECK
Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Accessories United Kingdom

Hexergo Dual Monitor Arm Black CTS203

4ZE1W59535

Lenovo DisplayPort to DisplayPort 1.4 cable 1.8m

4X91U92142

Lenovo Essential FHD Webcam Gen2

4XC1S15018

NanoSaver Cable Lock from Lenovo

4XE1L51710

ThinkVision MS30 Monitor Soundbar

4XD1J05151

Kensington Privacy Screen for Monitors 23.8" (16:9)

4Z11K07879

>> View More Accessories

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

ThinkVision T24-40 Monitor 64A4MAR2U1

Lenovo

PERFORMANCE

Display Size
23.8″

View Area
527x296.5 mm

Panel
In-Plane Switching

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920x1080

Pixel Pitch
0.2745x0.2745 mm

Dot / Pixel Per Inch
95 dpi

View Angle (H / V)
178° / 178°

Response Time
4ms GtG (Extreme mode) / 6ms GtG (Typical mode)

Color Support
16.7 Million

Refresh Rate
48Hz - 120Hz

Brightness
250 cd/m²

Contrast Ratio
1500:1

Color Gamut
99% sRGB, 99% BT.709

Screen Surface Treatment
Anti-glare

Curvature
Flat Panel

Camera
Modular Camera Support

Microphone
None

Speakers
Modular Speaker Support

Power Consumption (Typical / Maximum)
12W / 66W

Power Adapter
Integrated (special order with US 3-pin power cable)

DESIGN

Stand
Tilt, Swivel, Pivot, Height Adjust Stand

Case Color
Eclipse Black

Side Bezel Width
2 mm

Mounting
Supports VESA mount 100 x 100 mm

ThinkCentre M Series Support
Tiny Support

Dimensions (WxDxH)[1]
- Lowest Position | 539.8 x 190.0 x 350.8 mm (21.25 x 7.48 x 13.81 inches)
- Highest Position | 539.8 x 190.0 x 505.8 mm (21.25 x 7.48 x 19.91 inches)
- Head Only | 539.8 x 45.3 x 314.8 mm (21.25 x 1.78 x 12.39 inches)

Packaging Dimensions (WxDxH)
734.0 x 112.0 x 422.0 mm (28.90 x 4.41 x 16.61 inches)

Weight[2]
- Monitor With Stand | 5.1 kg (11.2 lbs)
- Monitor Head Only | 3.0 kg (6.6 lbs)

Packaging Weight
7.3 kg (16.1 lbs)

CONNECTIVITY

Rear Ports
- 1x USB-B (USB 5Gbps / USB 3.2 Gen 1), USB upstream
- 1x USB-C® (USB 5Gbps / USB 3.2 Gen 1) with 15W PD, data transfer only, USB downstream
- 3x USB-A (USB 5Gbps / USB 3.2 Gen 1, 1x BC 1.2), USB downstream
- 1x HDMI® 1.4, supports 1920x1080@120Hz
- 1x DisplayPort™ 1.2
- 1x VGA

SERVICE

Base Warranty
3-year limited warranty

CERTIFICATIONS

Environmental Certification
ENERGY STAR® Certified, TCO 10, TCO Edge 2.1, EPEAT Gold, EU Energy Efficiency Level (Level-C), Volatile Organic Compound Certification, RoHS

Ergonomic Certification
Eyesafe® Display 2.0, TÜV Rheinland® Low Blue Light (Hardware solution), TÜV Rheinland® Eye Comfort (5 Stars)

Sync Technology
None

Special Features
- Lenovo® ThinkColour (Lenovo® Accessories and Display Manager) Support Lenovo® ThinkColour supports Windows® 10 & 11, Mac OS (functions vary across systems) Lenovo® Accessories and Display Manager is formerly Lenovo® Display Control Center
- LDFM (Lenovo® Display Fleet Manager)
- Natural Low Blue Light

SOFTWARE

Operating System
Support Windows® 10, Windows® 11

ACCESSORIES

In the Box
- Monitor with stand
- 1x HDMI® cable
- 1x USB-B to USB-A Gen 1 cable (1.8m)
- 1x Power cable (1.8m)
- Quick setup guide

MODEL

Region	: EMEA
EAN / UPC / JAN	: 0199271574751 / 199271574751 / None
Announce Date	: 2025-05-30

Product image is a sample, it may not match the real color of this model

Note:
[1] The system dimensions may vary depending on configurations.
[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

- Please refer to the official Lenovo store website or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.