MPN: LV-6AFTP-FLEX-ANG-075B-S

Network Cable CAT6A U/FTP Slim & Bendable Halogenfree (LSZH) 7.5m Black

Lanview Slim & Bendable Cat6A Network Cable (LSZH).
Slim, bendable, and halogen-free, this Cat6A cable features a flexible plug that can be angled up to 90° in all four directions—perfect for tight spaces without compromising performance.
Optional color clips (sold separately) make it easy to organize and identify your cables.

Tip: Adjust the plug angle before inserting into the RJ45 jack to prevent damage.



- Wire number: 8 (4 x 2 twisted pair)
- Bending radius 4xOD
- Slim cable AWG 30
- Clips sold seperately
- Comes With Black Clips

Specifications

Features	**AWG wire size**	30
	Cable length	7.5 m
	Cable shielding	U/FTP (STP)
	Cable standard	Cat6a
	Cabling technology	10GBase-T
	Conductor material	Copper
	Conductor type	Cu
	Connector 1	RJ45
	Connector 1 form factor	Straight
	Connector 1 gender	Male
	Connector 2	RJ45
	Connector 2 form factor	Straight
	Connector 2 gender	Male
	Connector contacts plating	Gold
	Connector gender	Male
	Ethernet interface type	10 Gigabit Ethernet
	Jacket material	Aluminum
	Product colour	Black
	RoHS compliance	Yes
	Snagless cable boot	Yes
	Suitable for outdoor use	No
Legal Information	**ADR Information**	No restrictions
	Country of Origin	China

Legal Information	**EU ECCN Code**	N/A
	Tariff No.	8544421000
	UNSPSC Code	26121609
	US ECCN Code	EAR99
Other features	**Cable diameter**	3.8 mm
	Length	0.25 mm
Package dimensions	**Gross Weight (Package, kg)**	0.037 kg
Product dimensions	**Net Weight (Product, kg)**	0.031 kg
	Product Depth	13 cm
Vendor information	**Brand Name**	Lanview
	Warranty	25 Year(s)

Other products in this series

Cable length	Black	White
0.25	LV-6AFTP-FLEX-ANG-0025B-S	LV-6AFTP-FLEX-ANG-0025W-S
0.5	LV-6AFTP-FLEX-ANG-005B-S	LV-6AFTP-FLEX-ANG-005W-S
1	LV-6AFTP-FLEX-ANG-01B-S	LV-6AFTP-FLEX-ANG-01W-S
1.5	LV-6AFTP-FLEX-ANG-015B-S	LV-6AFTP-FLEX-ANG-015W-S
2	LV-6AFTP-FLEX-ANG-02B-S	LV-6AFTP-FLEX-ANG-02W-S
3	LV-6AFTP-FLEX-ANG-03B-S	LV-6AFTP-FLEX-ANG-03W-S
5	LV-6AFTP-FLEX-ANG-05B-S	LV-6AFTP-FLEX-ANG-05W-S
7.5	LV-6AFTP-FLEX-ANG-075B-S	LV-6AFTP-FLEX-ANG-075W-S
10	LV-6AFTP-FLEX-ANG-10B-S	LV-6AFTP-FLEX-ANG-10W-S

Other images



