ThinkPad T14s Gen 7 (AMD) 21YW001QAU





The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

- AMD Ryzen AI 7 PRO 450 (8C / 16T, 2.0 / 5.1GHz, 8MB L2 / 16MB L3)
- 32GB Soldered LPDDR5X-8000
- 512GB SSD M.2 2280 PCIe 4.0x4 NVMe Opal 2.0
- Integrated AMD Radeon 860M Graphics
- Windows 11 Pro, English (US) / English (UK)
- Case color - Blue
- CO2 Offset Service 200kg Gen 3 Commercial IDG, 3Y Premier Support for AIPC upgrade from 3Y Courier/Carry-in

Premier Support - A direct 24x7x365 line to our most elite technicians.

- Advanced technical support, 24x7x365, in more than 100 markets
- Comprehensive hardware & OEM software support
- Single point of contact for simplified end-to-end case management
- Technical Account Managers for proactive relationship and escalation management
- Priority on service delivery and repair parts
- Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Accessories

Denmark



Lenovo Dual-Mode Wireless ANC Headset 6550 (USB-C, Teams)

4XD1S19778



ThinkPad Rolling Wireless RW101R-GL SDX12 4G USB M.2 3042 module for CS2627

4XC1V64418



Lenovo 65W Mini USB-C GaN Charger

G0A665WBEU



ThinkPad USB4 Dock 5000 (with 135W Adapter)

40BF0135EU



ThinkPad 2TB Value PCIe Gen4 NVMe OPAL 2.0 M.2 2280 SSD III

4XB1V57576



ThinkPad Bluetooth Presenter Mouse (Aura Edition)

4Y51T62792

>> View More Accessories

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

ThinkPad T14s Gen 7 (AMD) 21YW001QAU

PERFORMANCE

Processor
AMD Ryzen™ AI 7 PRO 450 (8C / 16T, 2.0 / 5.1GHz, 8MB L2 / 16MB L3)

AI PC Category
Copilot+ PC[1]

NPU
Integrated AMD Ryzen™ AI, up to 50 TOPS

Graphics
Integrated AMD Radeon™ 860M Graphics

Chipset
AMD SoC Platform

Memory
32GB Soldered LPDDR5X-8000[2]

Memory Slots
Memory soldered to systemboard, no slots, dual-channel

Max Memory
32GB soldered memory, not upgradable

Storage
512GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Storage Slot
One M.2 2280 PCIe® 4.0 x4 slot

Max Storage Support[3]
One drive, up to 2TB M.2 2280 SSD

Optical
None

Card Reader
No Card Reader

Audio Chip
SoundWire®, Realtek® ALC3346 codec

Speakers
Stereo speakers, 2W x2, Dolby Atmos®

Microphone
2x, 360°

Camera
5.0MP + IR Discrete with Privacy Shutter, vHDR, Computer Vision on ISP

Battery
58Wh

Power Adapter
65W USB-C® (3-pin)

DESIGN

Display
14" WUXGA (1920x1200) IPS 500nits Anti-glare, 100% sRGB, 60Hz, Low Power, Touch[4]

Touchscreen
In-cell, 10-point Multi-touch

Screen-to-Body Ratio
88%

Pen
Pen Not Supported

Keyboard
Backlit, English

Dimensions (WxDxH)[5]
313 x 219.4 x 10.7/15.85 (front/rear), 18.56 (maximum) mm 12.32 x 8.64 x 0.42/0.62 (front/rear), 0.73 (maximum) inches

Weight[6]
Starting at 1.09 kg (2.40 lbs)

Case Color
Blue

Case Material
Carbon Fiber Hybrid (Top), Aluminium (Bottom)

SOFTWARE

Operating System
Windows® 11 Pro, English (US) / English (UK)

Bundled Software
Lenovo® AI Now

CONNECTIVITY

WLAN + Bluetooth
MediaTek Wi-Fi® 7 MT7925, 802.11be 2x2 + BT5.4

WWAN
Snapdragon® X61 5G Modem-RF System, 5G Sub-6 GHz, with Embedded eSIM

SIM Card
No physical SIM card inbox

Ethernet
No Onboard Ethernet[7]

NFC
No NFC

Standard Ports
- 1x USB-A (USB 5Gbps), Always On
- 1x USB-C® (USB 5Gbps), with USB PD 15-65W and DisplayPort™ 1.2
- 2x Thunderbolt™ 4, with USB PD 15-65W and DisplayPort™ 2.1
- 1x HDMI® 2.1, up to 4K/60Hz
- 1x Headphone / microphone combo jack (3.5mm)

Optional Ports (configured)
1x Nano-SIM Card Slot

Docking
Various docking solutions supported via Thunderbolt™ / USB-C®. For more compatible docking solutions, please visit Docking for ThinkPad® T14s Gen 7 (AMD)

SECURITY & PRIVACY

ThinkShield
ThinkShield is a comprehensive security solution that encompasses hardware, software, and supply chain components. For more detials, visit here

Security Chip
Discrete TPM 2.0 Enabled

Physical Locks
Kensington Nano Security Slot™, 2.5 x 6 mm

Smart Card Reader
No Smart Card Reader

Fingerprint Reader
Touch Style, Match-on-Chip, Integrated in Power Button

Other Security
- Computer Vision-based Human Presence Detection on Image Signal Processor (ISP)
- Camera privacy shutter
- IR camera for Windows® Hello (facial recognition)

MANAGEABILITY

System Management
DASH

SERVICE

Base Warranty
3-year, Courier or Carry-in with 1-year Battery

Included Upgrade
CO2 Offset Service 200kg Gen 3 Commercial IDG, 3Y Premier Support for AIPC upgrade from 3Y Courier/Carry-in

ACCESSORIES

Bundled Accessories
None

CERTIFICATIONS

Green Certifications
- ENERGY STAR® 9.0
- EPEAT™ Gold Registered[8]
- ErP Lot 6/26
- RoHS compliant
- TCO Certified, generation 10

Mil-Spec Test
MIL-STD-810H military test passed

Other Certifications
Eyesafe® Certified 2.0

MODEL

TopSeller	: Yes	**EAN / UPC / JAN**	: 199275824364
Announce Date	: 2026-05-13	**End of Support**	: 2032-12-13

- Please refer to the official Lenovo store website or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.
- To view full note details, please visit the web page.