ThinkPad T14s Gen 4 (AMD)

Designed for business travelers, this laptop powered by up to AMD Ryzen 7 pro processor lets users debug processes and manage projects effortlessly. AMD Radeon 740M or 780M graphics offer high performance, allowing content creators to work with high-resolution images, videos, and 3D content more smoothly and efficiently. Moreover, with up to 32GB LPDDR5 memory and up to 2TB SSD storage, this laptop easily accommodates large software databases, multimedia files, and work documents.

Redefining possibilities with powerful performance and groundbreaking on-device AI

The ultimate productivity notebook, ThinkPad T Series will keep users productive all day with long battery life, docking and enhanced connectivity options, security and manageability features.

Experience superior audio quality with 2W dual Dolby Audio stereo speakers, perfect for conference calls and multimedia presentations. The optional FHD 1080p camera with privacy shutter ensures crisp video quality and security for professionals on the go.

Security features include BIOS security and discrete TPM 2.0 chipset that ensures robust protection for sensitive data, crucial for content creators handling proprietary content.

With the latest AMD processors, ultra-fast SSD storage and modern features, this laptop enables mobile users to work with optimal efficiency.

Updated 2024-10-11

Lenovo Services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..

Return To Depot Repair Warranty

- No-hassle repair process at a Lenovo service center
- Lenovo pays for all shipping between the customer and service facility
- Avoid unplanned operational expense with a simple annual fee

Accessories

Thinkpad Essential 16" Backpack (Eco)

- Two internal compartments (one for notebooks up to 16"), two front zipper pockets, and one side mesh water bottle sleeve that ensure you'll never run out of space.
- A padded top handle. And a rear luggage strap. Every feature is crafted for convenience and comfort.
- Elegant black nylon exterior, grey interior lining, and a splash of red accents.

PN: 4X41C12468

Lenovo Essential USB Mouse

- Convenient and easy plug-and-play connection to PCs via a USB cable
- Ergonomic full-size design provides a comfortable grip for all day comfort
- Ambidextrous design, high-resolution 1600 DPI optical sensor experience smooth movment

PN: 4Y50R20863

ThinkPad T14s Gen 4 (AMD)

Performance

Processor
AMD Ryzen 5 / 7

Operating System
Windows 11 Pro
Windows 11 Home
Windows 11 Home Single Language
Windows 11 DG Windows 10 Pro 64
Windows 10 IoT Enterprise LTSC 2021
Linux
Ubuntu Linux

NPU [2]
AMD Ryzen AI, up to 10 TOPS*

[2]Only for the models with AMD Ryzen 7 PRO 7840U processor.

Graphics
AMD Radeon 740M (integrated)
AMD Radeon 780M (integrated)

Memory
16GB LPDDR5-6400, soldered
32GB LPDDR5-6400, soldered

Storage [3]
Up to 1x 2TB M.2 2280 PCIe NVMe SSD

[3]The storage capacity supported is based on the test results with current Lenovo storage offerings.

Audio
High Definition (HD) Audio
Stereo speakers, 2W x2, Dolby Audio
Dual-microphone array, 360° far-field, Dolby Voice*

Camera*
FHD 1080p, with privacy shutter
5.0MP + IR discrete, with privacy shutter

Battery [4 5]
57Wh (up to 15.67 hr) battery, Rapid Charge

[4]Battery life claims are approximate maximum. Actual result will vary depending on many factors and the maximum battery capacity will decrease with time and use.

[5]Rapid charge is only guaranteed when the computer is turned off or in standby mode or in hibernation mode.

Power Adapter*
45W USB-C adapter, PD 3.0
65W USB-C adapter, PD 3.0
65W USB-C slim adapter, PD 3.0

Design

Display [6]
14" WUXGA (1920x1200) IPS Anti-glare 16:10
- 300nits, 45% NTSC
- 300nits, 45% NTSC, touch
- 400nits, 100% sRGB, low power, Eyesafe
- 500nits, 100% sRGB, touch, ThinkPad Privacy Guard

14" 2.2K (2240x1400) IPS Anti-glare 16:10
- 300nits, 100% sRGB, TÜV Low Blue Light (Hardware Solution)

14" 2.8K (2880x1800) OLED AGARAS 16:10
- 400nits, 100% DCI-P3, DisplayHDR True Black 500, Dolby Vision, Eyesafe

[6]IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Keyboard
6-row, spill-resistant, optional backlight

Touchpad
TrackPoint and glass-like Mylar surface touchpad
61 x 115 mm (2.40 x 4.53 inches)

Dimensions [7]
317.5 x 226.9 x 16.9 mm (12.5 x 8.93 x 0.67 inches)

[7]The system dimensions may vary depending on configurations.

Weight [8]
Starting at 1.26 kg (2.77 lbs)

[8]The system weight is approximate and may vary depending on configurations

Color
Deep black
Storm grey

Case material
Carbon fiber hybrid or aluminium (top)
Aluminium (bottom)

Connectivity

WLAN + Bluetooth* [9 10]
802.11ax (Wi-Fi 6E), Bluetooth 5.3

[9]Wi-Fi 6E is only enabled on Windows 11 and operates as Wi-Fi 6 with Windows 10.

[10]Bluetooth 5.3 operation requires Windows 11.

WWAN*
4G LTE CAT4
4G LTE CAT16
5G Sub-6 GHz with embedded eSIM

NFC
Near Field Communication*

Ports
1x USB 3.2 Gen 1
1x USB 3.2 Gen 1 (Always On)
2x USB4 40Gbps (data, PD 3.0, DP 1.4a)
1x HDMI 2.1, up to 4K/60Hz
1x Headphone / microphone combo jack (3.5mm)
1x Smart card reader*
1x Nano-SIM card slot (WWAN support models)*

Docking
Docking support via USB-C

Security & Privacy

Security
Discrete TPM 2.0 and Microsoft Pluton TPM 2.0
Kensington Nano Security Slot
Smart card reader, supports ISO 7816 and EMV*
Touch style MOC fingerprint reader*
Camera privacy shutter*
IR camera for Windows Hello (facial recognition)*
Privacy Guard with Privacy Alert*
Glance by Mirametrix
Ultrasonic Human Presence Detection*

Manageability

System Management*
DASH*

Certifications

Green Certifications [11 12 13]
ENERGY STAR 8.0
EPEAT Gold Registered
ErP Lot 6/26
TCO Certified 9.0
RoHS compliant

[11]The items listed under the "Green Certifications" sectior may not only refer to certification but also registration a self-declaration.

[12]EPEAT registration and ENERGY STAR certification are dependent on system OS.

[13]EPEAT is registered where applicable, please see epeat.net for registration status by country.

Other Certifications
Eyesafe Certified*
TÜV Rheinland Low Blue Light (Hardware Solution)*
MIL-STD-810H

Items with * are optional and only available on selected models. Information presented here may represent the maximum possible configurations for this product, but it does not necessarily reflect what is available in your region. Please ask your rep or check the specifications for specific Part Numbers in your region. © 2024 Lenovo. Products are available while supplies last. Lenovo is not responsible for photographic or typographic errors. Lenovo, the Lenovo logo, ThinkPad, ThinkCentre, ThinkBook, ThinkStation and ThinkVision are trademarks or registered trademarks of Lenovo. 3rd party product and service names may be trademarks of others. Depending on factors such as the processing capability of peripheral devices, file attributes, system configuration and operating environments, the actual data transfer rate of USB connectors will vary and is typically slower than published standards.