LCD DISPLAY

VX2757-2K-PRO

Key **Features**

- 27” SuperClear® IPS panel
- 200Hz Refresh rate delivers fluid visuals
- 2K QHD resolution for incredible detail
- Rapid 1ms MPRT for crisp image
- NVIDIA G-Sync Compatible for seamless gameplay

Product **Description**

The ViewSonic VX2757-2K-PRO features a 27” QHD display. The hyper-responsive 200Hz refresh rate renders your games with ultra-smooth graphics. The monitor’s variable refresh rate prevents screen tearing and stuttering for fluid gameplay and the 1ms MPRT response time enables you to react in-game with speed and precision. Equipped with SuperClear® IPS technology, it boasts wide viewing angles and breathtaking visuals, perfect for immersive gaming sessions, creative endeavors, and efficient office work. Beyond performance, the monitor's sleek design elevates your workspace aesthetics, combining form and function for a complete package.

1. VESA Wall Mount Compatible(75x75mm)
2. DC
3. HDMI 2.0 * 2
4. Display Port 1.4
5. Audio Out

Visit Us www.viewsonic.com

DISPLAY

Display Size (in.):	27
Viewable Area (in.):	27
Panel Type:	IPS Technology
Resolution:	2560 x 1440
Resolution Type:	QHD (Quad HD)
Static Contrast Ratio:	1,000:1 (typ)
Dynamic Contrast Ratio:	80M:1
High Dynamic Range:	HDR10
Light Source:	LED
Brightness:	300 cd/m² (typ)
Colors:	1.07B
Color Space Support:	10 bit (8 bit + FRC)
Aspect Ratio:	16:9
Response Time (MPRT):	1ms
Viewing Angles:	178º horizontal, 178º vertical
Backlight Life (Hours):	30000 Hrs (Min)
Curvature:	Flat
Refresh Rate (Hz):	200
Variable Refresh Rate Technology:	Yes (G-Sync compatible)
Low Blue Light:	Hardware and software solution
Flicker-Free:	Yes
Color Gamut:	DCI-P3: 90% coverage (Typ) NTSC: 89% size (Typ) sRGB: 126% size (Typ)
Pixel Size:	0.233 mm (H) x 0.233 mm (V)
Surface Treatment:	Anti-Glare, Hard Coating (3H)

COMPATIBILITY

PC Resolution (max):	2560x1440
Mac® Resolution (max):	2560x1440
PC Operating System:	Windows 10/11 certified; macOS tested
Mac® Resolution (min):	2560x1440

CONNECTOR

3.5mm Audio Out:	1
HDMI 2.1:	2
DisplayPort:	1
Power in:	DC Socket (Center Positive)

POWER

Eco Mode (Conserve):	21W
Eco Mode (optimized):	26W
Consumption (typical):	32W
Consumption (max):	36W
Voltage:	AC 100-240V
Stand-by:	0.5W
Power Supply:	External Power Adaptor

ADDITIONAL HARDWARE

Kensington Lock Slot:	1

CONTROLS

Physical Controls:	Up, Right, Down, Left, Power
On Screen Display:	Input Select, Audio Adjust, ViewMode, Color Adjust, Manual Image Adjust, Setup Menu

OPERATING CONDITIONS

Temperature:	32°F to 104°F (0°C to 40°C)
Humidity (non-condensing):	20% to 90%

WALL MOUNT

VESA Compatible:	75 x 75 mm

INPUT SIGNAL

Frequency Horizontal:	HDMI (v2.1): 31 ~ 215KHz, DisplayPort (v1.4): 31 ~ 295KHz
Frequency Vertical:	HDMI (v2.1): 48 ~ 144Hz, DisplayPort (v1.4): 48 ~ 200Hz

VIDEO INPUT

Digital Sync:	TMDS - HDMI (v2.1), PCI-E - DisplayPort (v1.4)

ERGONOMICS

Tilt (Forward/Back):	-5º / 15º

WEIGHT (IMPERIAL)

Net (lbs):	9
Net Without Stand (lbs):	7.3
Gross (lbs):	12.1

WEIGHT (METRIC)

Net (kg):	4.1
Net Without Stand (kg):	3.3
Gross (kg):	5.5

DIMENSIONS (IMPERIAL) (WXHXD)

Packaging (in.):	26.6 x 18 x 4.2
Physical (in.):	24.14 x 17.71 x 7.48
Physical Without Stand (in.):	24.14 x 14.29 x 2.08

DIMENSIONS (METRIC) (WXHXD)

Packaging (mm):	676 x 458 x 107
Physical (mm):	613.19 x 449.89 x 190
Physical Without Stand (mm):	613.19 x 362.99 x 52.74

GENERAL

Regulations:	CE, CE EMC, CB, RoHS, ErP, REACH, WEEE, EAC, UkrSEPRO
PACKAGE CONTENTS:	VX2757-2K-PRO x1, DisplayPort Cable (v1.4; Male-Male) x1, AC/DC Adapter x1, Quick Start Guide x1, Power plug x1 or 2 (by country)
Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.
Warranty:	*Warranty offered may differ from market to market

Copyright © ViewSonic Corporation 2000-2026. All rights reserved.