Lenovo Chrome 14ITN11 83SV000EUS





- Intel Core™ 3 N355 (8C / 8T, Max Turbo up to 3.9GHz, 6MB Intel® Smart Cache)
- 8GB Soldered LPDDR5X-4800
- 128GB UFS 2.2
- Integrated Intel® Graphics
- ChromeOS
- Case color - Luna Grey
- 1-year, Mail-in

The product images are for illustration purposes only. Actual product appearance, ports, keyboard layout, and accessories may vary by model.

Premium Care - Advanced Support from Real People. Real Fast.

REAL PERSON
Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

REAL FAST
Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

HASSLE FREE
'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

PC HEALTH CHECK
Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Recommended Accessories

United Kingdom



Lenovo 900 Multi-Device Wireless Mouse

GY51V37443



Lenovo 16" Laptop Topload T210 Beige (ECO)

GX41W44768



Lenovo 65W Mini USB-C GaN Charger

G0A665WBUK



Lenovo USB 20Gbps USB-C to USB-C Cable 1.5m

4X91U92143



Lenovo Analog In-Ear Headphones Gen II Bulk Package (20pcs)

4XD1T54899



Lenovo PS8S Portable SSD 4TB

4XB1T91892

>> View More Accessories

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Lenovo Chrome 14ITN11 83SV000EUS

PERFORMANCE

Processor
Intel Core™ 3 N355 (8C / 8T, Max Turbo up to 3.9GHz, 6MB Intel® Smart Cache)

Graphics
Integrated Intel® Graphics

Chipset
Intel® SoC Platform

Memory[1]
8GB Soldered LPDDR5X-4800

Memory Slots
Memory soldered to systemboard, no slots

Max Memory
8GB soldered memory, not upgradable

Storage
128GB UFS 2.2[2]

Storage Slot
UFS on systemboard, no slots

Max Storage Support[3]
128GB UFS 2.2 on systemboard

Card Reader
No Card Reader

Audio Chip
High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers
Stereo speakers, 2W x2, optimized with Waves MaxxAudio®

Microphone
2x, Array

Camera
5.0MP with Privacy Shutter

Battery
50Wh

Power Adapter
65W USB-C® (2-pin)

DESIGN

Display
14″ WUXGA (1920x1200) IPS 400nits Anti-glare, 45% NTSC[4]

Touchscreen
None

Screen-to-Body Ratio
87%

Pen
Pen Not Supported

Keyboard
Backlit, English

Touchpad
Buttonless Mylar® surface multi-touch touchpad, 75 x 120 mm (2.95 x 4.72 inches)

Dimensions (WxDxH)[5]
319.2 x 223.3 x 19.9 mm (12.57 x 8.79 x 0.78 inches)

Weight[6]
Starting at 1.36 kg (2.99 lbs)

Case Color
Luna Grey

Case Material
PC-ABS (Top), PC-ABS (Bottom)

Surface Treatment
Painting (Top), Texture (Bottom)

SOFTWARE

Operating System
ChromeOS

Bundled Software
None

CONNECTIVITY

WLAN + Bluetooth
Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3

WWAN
WWAN Not Supported

Ethernet
No Onboard Ethernet

Standard Ports
- 2x USB-A (USB 5Gbps)
- 2x USB-C® (USB 10Gbps), with USB PD 45-65W and DisplayPort™ 1.4
- 1x HDMI® 1.4b
- 1x Headphone / microphone combo jack (3.5mm)

Docking
Various docking solutions supported via USB-C®. For more compatible docking solutions, please visit Docking for Lenovo® Chrom 14ITN11

SECURITY & PRIVACY

Security Chip
Google Security Chip H1

Physical Locks
Kensington Nano Security Slot™, 2.5 x 6 mm

Fingerprint Reader
No Fingerprint Reader

Other Security
Camera privacy shutter

SERVICE

Base Warranty
1-year, Mail-in

Included Upgrade
None

ACCESSORIES

Bundled Accessories
None

CERTIFICATIONS

Green Certifications
- ENERGY STAR® 9.0
- EPEAT 2.0 Gold Registered
- ErP Lot 6/26
- RoHS compliant
- TCO Certified, generation 10

Mil-Spec Test
MIL-STD-810H military test passed

Other Certifications
TÜV Rheinland® Low Blue Light (Software Solution)

MODEL

Product	: Lenovo® Chrome 14ITN11 | Lenovo® Chromebook Plus Enterprise i (14″, 11)		
TopSeller	: Yes	**EAN / UPC / JAN**	: 199276810984
Announce Date	: 2026-05-19	**End of Support**	: N/A

Note:
[1] Installed memory is actually LPDDR5X-6400 but may run as LPDDR5X-4800 due to platform limitations.
[2] UFS 2.2 storage is downgraded to closer to UFS 2.1 due to platform limitations.
[3] The storage capacity supported is based on the test results with current Lenovo storage offerings.
[4] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.
[5] The system dimensions may vary depending on configurations.
[6] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

- Please refer to the official Lenovo store website or contact a local Lenovo sales representative or authorized business partner for current inventory and purchase options.
- Lenovo reserves the right to change specifications without notice.
- California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: https://www.calrecycle.ca.gov/Electronics/Consumer