

Part No	**90PT03XA-M0BRK0**
Sales Model Name	**V440VA-DICWPC028W**
EAN Code	**4711636527446**
UPC Code	**199291527447**
BASE UNIT	**VSPT03X5-BU0040**
ID Color	**White**
Panel Size	**23.8-inch**
Resolution	**FHD (1920 x 1080) 16:9**
Panel Tech	**LCD**
Brightness	**250nits**
NTSC %	**sRGB: 100%**
View angle(H/V)	**178/178**
Response time(Typ/Max) (ms)	**14/25**
Refresh rate	**100Hz**
Contrast (Typ)	**1000:1**
Screen-to-body ratio	**93 %**
IPS-level	**Wide view**
Glare	**Anti-glare display**
Touch Panel	**Non-touch screen**
Stand type	**Normal Stand**
On board processor	**Intel® Core™ 5 Processor 210H 2.2 GHz (12MB Cache, up to 4.8 GHz, 8 Cores, 12 Threads)**
Chipset	**N/A**
VRAM	**N/A**
Integrated GPU	**Intel® Graphics**
DIMM Memory	**8GB DDR5 SO-DIMM**
Total System Memory	**DDR5 8GB**
Storage	**512GB M.2 NVMe™ PCIe® 4.0 SSD**
Easy Upgrade	**Not available**
Expansion Slot(includes used)	**2x DDR5 SO-DIMM slot**
Wireless	**Wi-Fi 6(802.11ax) (Dual band) 2*2 + Bluetooth® 5.4 Wireless Card**
LAN	**Realtek RTL8111H 10/100/1000 Mbps**
Front-facing camera	**1080p FHD camera**
Privacy Shutter	**With privacy shutter**
Harman/Kardon	**N/A**
Audio	**Built-in array microphone** **Built-in speakers**

Operating System	**Windows 11 Home - ASUS recommends Windows 11 Pro for business**
Office	**1-month trial for new Microsoft 365 customers. Credit card required.**
AC Adapter	**ø4.5, 120W AC Adapter, Output: 20V DC, 6.0A, 120W, Input: 100~240V AC 50/60Hz universal**
Side I/O Port	**1x Kensington lock** **1x 3.5mm combo audio jack** **1x USB 2.0 Type-A**
Back I/O Port	**1x DC-in** **1x RJ45 Gigabit Ethernet** **1x HDMI out 1.4** **1x USB 3.2 Gen 1 Type-C** **3x USB 3.2 Gen 1 Type-A**
Dimension (WxHxD)	**54.1 x 41.6 x 1.7 ~ 24.4 cm (21.30" x 16.38" x 0.67" ~ 9.61")**
Weight	**05.46 kg (12.04 lbs)**
Security	**BIOS Booting User Password Protection** **HDD User Password Protection and Security** **Kensington Security Slot™(7x 3mm)**
Antivirus	**McAfee® 30 days free trial**
Trusted Platform Module	**Trusted Platform Module (Firmware TPM)**
Built-in Apps	**AI ExpertMeet (AI features need devices with 12GB RAM or more)** **MyASUS** **ASUS Business Manager**
My ASUS features	**System diagnosis** **Fan Profile** **Splendid** **AppDeals** **Link to MyASUS**
MyExpert Features	**N/A**
Included in the box	**Wireless sandstone white keyboard** **Wireless optical mouse**
Keyboard language	**French**
Ecolabels & Compliances	**EPEAT Gold** **Energy star 9.0** **REACH** **RoHS**
Base Warranty	**2Y Pick up/ return**
Recommended Warranty Package Part number//Extension and/or upgrade service from base warran	**ACX10-004016PT//1Y Extension** **ACX13-010600PT//1Y Extension; 3Y OnSite Service(Next Business Day)*upgrade** ***If you would like to know the details, please contact your sales teams.**
Sustainable Material_Rear	**65% PCR recycled plastic rear cover**
Sustainable Material_Base	**65% PCR recycled plastic base cover**
Sustainable Material_Total PCR recycled plastic	**55%**